



LFH2002009016

Trunking halogen free LFH 20x20mm traffic white

Technical Features

Dimensions

Height	18 mm
Width	19 mm
Length	2000 mm
Lid width	19 mm

Cover, door

Number of mountable lids	1
Type of lid	Premounted

Dimensions

Inner cross-section	228 - 228 mm ²
---------------------	---------------------------

Capacity

Max. number of cables (Ø11mm, 50% filled, without devices)	1
--	---

Materials

Material	PC-ABS
Treatment	Untreated
RAL code	9016
Colour	Traffic white
Transparent	No

Safety

Impact resistance IK	IK07
Ingress Protection (IP) class	IP30

Standards

Suitable for functional integrity according to DIN4102-12	No
---	----

Use conditions

Operating temperature	-5 - 90 °C
-----------------------	------------

Connectivity

Trunking coupling	Without coupling
-------------------	------------------

Equipment

Number of partitions	0
Number of compartments	1 - 1
Number of pluggable partitions	0
Cable retaining clip included	No
Number of cable retainers per meter	0
With protective film	No

Installation, mounting

Base perforation	Yes
------------------	-----

Configuration

Is self-adhesive	No
With antibacterial treatment	No

Scope of delivery

Delivery on roll	No
------------------	----

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

