



SPA180N

**Combined SPD T1+T2 1P N-PE Iimp 100kA Uc 1.5KV remote contact integrated fuse**

**Technical Features**

**Electric current**

Lightning impulse current Iimp (10/350 μs) IEC 61643 L-N(PEN)/ N-PE 100 kA

**Network configuration**

Network type TT TN-S

**Equipment**

With remote signalling contact Yes

**Standards**

Requirement class IEC 61643 T1 T2

**Capacity**

Number of modules 2

**Safety**

Ingress Protection (IP) class IP20

**Electric current**

Max. discharge (Imax) L-N(PEN)/ N-PE 100 kA

**Use conditions**

Operating temperature -40 - 80 °C

**Dimensions**

Height 95.20 mm

Width 35.60 mm

Depth 67 mm

**Controls and indicators**

Indicator lamp Optic

**Connection**

Cross-section of input and output with screws, for flexible conductors 2.5 - 35 mm<sup>2</sup>

Cross-section of input and output with screws, for massive conductors 2.5 - 35 mm<sup>2</sup>

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes