



VF10101SPD

Volta 4Row 7W 1RCD - 2x6A Ltg. RCBOs SPD

Technical Features

Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Flush mounting

Electric current

Rated current	63 A
---------------	------

Equipment

Number of rails	4
Number of rows	4
With lock	No

Capacity

Number of modules	48
-------------------	----

Dimensions

Height	755 mm
Width	348 mm
Depth	94.50 mm

Cover, door

Number of cabinet doors	1
-------------------------	---

Dimensions

Built-in depth	89 mm
----------------	-------

Cover, door

Number of locks	0
-----------------	---

Dimensions

Number of width units	12
-----------------------	----

Cover, door

Door/cover is transparent	No
---------------------------	----

Materials

Material	Plastic
RAL code	9010
Colour	Pure white

Equipment

Has mounting plate	No
--------------------	----

Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP30
Locking type	Snap on lock
Glow wire test	650 °C