



JK116BGSPD

125A 12 Way TPN Board with 4 pole SD & Type II SPD Glazed

Technical Features

Installation, mounting

| | |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

Functions

| | |
|----------------------------|-----|
| Has protection main switch | Yes |
| Overvoltage protection | No |

Capacity

| | |
|-------------------|----|
| Number of modules | 36 |
|-------------------|----|

Electric current

| | |
|---------------|-------|
| Rated current | 125 A |
|---------------|-------|

Dimensions

| | |
|-----------------------|-----------|
| Depth | 132.50 mm |
| Height | 850 mm |
| Width | 465 mm |
| Thickness of sidewall | 0.90 mm |

Cover, door

| | |
|---------------------------|-----|
| Interlockable | Yes |
| Door/cover is transparent | Yes |

Materials

| | |
|----------|------------|
| RAL code | 7035 |
| Colour | Light grey |
| Material | Steel |

Equipment

| | |
|--------------------|-----|
| Extension possible | Yes |
| With socket outlet | No |

Safety

| | |
|---|-------------------|
| Ingress Protection (IP) class | IP30 |
| Protection class | Isolation class I |
| Number of earth leakage switches 300 mA | 0 |

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|