



JK116BGSPD

**125A 24 Way TPN Board with 4 pole SD & Type II SPD Glazed**

**Technical Features**

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Functions**

Has protection main switch	Yes
Overvoltage protection	No

**Capacity**

Number of modules	72
-------------------	----

**Electric current**

Rated current	125 A
---------------	-------

**Dimensions**

Depth	132.50 mm
Height	1250 mm
Width	465 mm
Thickness of sidewall	0.90 mm

**Cover, door**

Interlockable	Yes
Door/cover is transparent	Yes

**Materials**

RAL code	7035
Colour	Light grey
Material	Steel

**Equipment**

Extension possible	Yes
With socket outlet	No

**Safety**

Ingress Protection (IP) class	IP30
Protection class	Isolation class I
Number of earth leakage switches 300 mA	0

**Sustainability**

RoHS conform	Yes
--------------	-----