



VME10910SPD

**9+10 Way 100A Switch Disconnecter Incomer + SM Type II SPD 2 Row**

**Technical Features**

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Architecture**

Number of poles	2
-----------------	---

**Functions**

Has protection main switch	Yes
Overvoltage protection	Yes

**Installation, mounting**

Suitable for outdoor usage	No
----------------------------	----

**Configuration**

Number of arc fault detection devices AFDD	0
--	---

**Capacity**

Number of modules	19
-------------------	----

**Electric current**

Rated current	110 A
---------------	-------

**Weight**

Weight	6.1 kg
--------	--------

**Dimensions**

Depth	102.5 mm
Height	480 mm
Width	293 mm

**Cover, door**

Interlockable	No
Door/cover is transparent	No

**Materials**

RAL code	9010
Colour	White
Material	Steel

**Connection**

Number of conduit inlets	0
Number of accessible phases	1

**Scope of delivery**

Number of RCCB in enclosure	0
-----------------------------	---

**Equipment**

Number of rows	2
Number of rails	2
Extension possible	No
With bell transformer	No
With socket outlet	No

**Safety**

Impact resistance IK	IK05
Ingress Protection (IP) class	IP4X
Number of earth leakage switches 30 mA	0
Number of earth leakage switches 300 mA	0

**Compatibility**

Cooker group suitable as power current group	Yes
--	-----

---

**Sustainability**

---

RoHS conform

Yes