



VMEF113SPD

**13 Way 100A Switch Disconnecter Incomer Single Mod Type II SPD Flush**

**Technical Features**

**Installation, mounting**

Mounting on	Flush mounting Flush-mounted frame Hollow wall
-------------	--

**Architecture**

Number of poles	2
-----------------	---

**Functions**

Has protection main switch	Yes
Overvoltage protection	Yes

**Installation, mounting**

Suitable for outdoor usage	No
----------------------------	----

**Configuration**

Number of arc fault detection devices AFDD	0
--	---

**Capacity**

Number of modules	13
-------------------	----

**Electric current**

Rated current	116 A
---------------	-------

**Weight**

Weight	4.2 kg
--------	--------

**Dimensions**

Depth	72 mm
Internal depth	72 mm
Height	282 mm
Width	407 mm
Number of width units	13
Thickness of sidewall	1 mm

**Cover, door**

Interlockable	No
Door/cover is transparent	No

**Materials**

RAL code	9010
Colour	White
Material	Steel

**Connection**

Number of conduit inlets	0
Number of accessible phases	1

**Scope of delivery**

Number of earth leakage circuit breaker type A	0
Number of RCCB in enclosure	0

**Equipment**

Number of groups	0
Number of light groups	0
Number of rows	1
With energy meter	No
Number of rails	1
Extension possible	No
With bell transformer	No
With socket outlet	No

---

**Safety**

Impact resistance IK	IK05
Ingress Protection (IP) class	IP4X
Number of earth leakage switches 30 mA	0
Number of earth leakage switches 300 mA	0

**Compatibility**

Cooker group suitable as power current group	No
--	----

**Sustainability**

RoHS conform	Yes
--------------	-----