



VMEF119SPD

19 Way 100A Switch Disconnecter Incomer Single Mod Type II SPD Flush

Technical Features

Installation, mounting

Mounting on	Hollow wall
-------------	-------------

Architecture

Number of poles	2
-----------------	---

Functions

Has protection main switch	Yes
Overvoltage protection	Yes

Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Configuration

Number of arc fault detection devices AFDD	0
--	---

Capacity

Number of modules	19
-------------------	----

Electric current

Rated current	116 A
---------------	-------

Weight

Weight	5.1 kg
--------	--------

Dimensions

Depth	104 mm
Internal depth	72 mm
Height	282 mm
Width	515 mm
Number of width units	19
Thickness of sidewall	1 mm

Cover, door

Interlockable	No
Door/cover is transparent	No

Materials

RAL code	9010
Colour	White
Material	Steel

Connection

Number of conduit inlets	0
Number of accessible phases	1

Scope of delivery

Number of earth leakage circuit breaker type A	0
Number of RCCB in enclosure	0

Equipment

Number of groups	0
Number of light groups	0
Number of rows	1
With energy meter	No
Number of rails	1
Extension possible	No
With bell transformer	No
With socket outlet	No

Safety

Impact resistance IK	IK05
Ingress Protection (IP) class	IP4X
Number of earth leakage switches 30 mA	0
Number of earth leakage switches 300 mA	0

Compatibility

Cooker group suitable as power current group	No
--	----

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes