



VF8101

**Volta 2Row 7W 1RCD - 2x6A Ltg. RCBOs**

**Technical Features**

**Voltage**

Nominal voltage	400 - 400 V
-----------------	-------------

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Flush mounting

**Electric current**

Rated current	63 A
---------------	------

**Equipment**

Number of rails	2
Number of rows	2
With lock	No
Has neutral terminal block	Yes

**Capacity**

Number of modules	24
-------------------	----

**Dimensions**

Height	505.50 mm
Width	348 mm
Depth	94.50 mm
Built-in width	314 mm

**Cover, door**

Number of cabinet doors	1
-------------------------	---

**Dimensions**

Built-in depth	89 mm
----------------	-------

**Cover, door**

Number of locks	0
-----------------	---

**Dimensions**

Number of width units	12
-----------------------	----

**Cover, door**

Door/cover is transparent	No
Cabinet door type	Single door

**Materials**

Material	Plastic
RAL code	9010
Colour	Pure white

**Equipment**

Has earthing terminal block	Yes
Has mounting plate	No

**Safety**

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP30
Locking type	Snap on lock
Glow wire test	650 °C
Protection class with door	IP30

**Sustainability**

RoHS conform	Yes
--------------	-----