



VF9101

Volta 3Row 7W 1RCD - 2x6A Ltg. RCBOs

Technical Features

Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Flush mounting

Electric current

Rated current	63 A
---------------	------

Equipment

Number of rails	3
Number of rows	3
With lock	No
Has neutral terminal block	Yes

Capacity

Number of modules	36
-------------------	----

Dimensions

Height	630.50 mm
Width	348 mm
Depth	94.50 mm
Built-in width	314 mm

Cover, door

Number of cabinet doors	1
-------------------------	---

Dimensions

Built-in depth	89 mm
----------------	-------

Cover, door

Number of locks	0
-----------------	---

Dimensions

Number of width units	12
-----------------------	----

Cover, door

Door/cover is transparent	No
Cabinet door type	Single door

Materials

Material	Plastic
RAL code	9010
Colour	Pure white

Equipment

Has earthing terminal block	Yes
Has mounting plate	No

Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP30
Locking type	Snap on lock
Glow wire test	650 °C
Protection class with door	IP30