




ZAX006E / ZAX007E / ZAX103E

(EN) Mounting instructions

(FR) Notice d'instructions

(DE) Montageanleitung

(NL) Montage instructie

(DA) Monteringsvejledning

(FI) Asennusohje

(NO) Montasjeanvisning

(SV) Monterings instruktioner

(IT) Istruzioni di montaggio

(ES) Instrucciones de montaje

(PT) Instruções de montagem

(CS) Montážní návod

(BS) Uputstvo za montažu

(UK) Інструкції з установки

(HR) Upute za montažu

(HU) Szerelési útmutató

(LT) Montavimo instrukcija

(LV) Montāžas instrukcija

(PL) Instrukcja montażowa

(RO) Instrucțiuni de montare

(SK) Návod na montáž

(RU) Указания по установке

(BG) Инструкции за монтаж





(EL) Οδηγίες τοποθέτησης

(SL) Navodilo za montažo


(EE) Paigaldusjuhised

(IS) Leiðbeiningar


(AR) دليل التركيب



a




2x



ZAX006E / ZAX007E


b









2x

2x


4x




ZAX103E




04a




05a




06a




07a




08a




01b




02b




03b




04b




05b




06b




07b




08b




09b




i



10






ZAY95075

ZAX006E



ZAX007E



ZAX103E

