



WPPS32

10AX 3 Gang 2 Way Wall Switch & Back Box with Knockouts

Technical Features

|                         |      |
|-------------------------|------|
| <b>Electric current</b> |      |
| Switching current       | 10 A |

|                               |                |
|-------------------------------|----------------|
| <b>Installation, mounting</b> |                |
| Mounting on                   | Flush mounting |

|                |       |
|----------------|-------|
| <b>Voltage</b> |       |
| Rated voltage  | 250 V |

|                  |        |
|------------------|--------|
| <b>Materials</b> |        |
| Colour           | Grey   |
| Surface finish   | Glossy |
| Material         | Steel  |
| Treatment        | Epoxy  |

|                       |                                     |
|-----------------------|-------------------------------------|
| <b>Identification</b> |                                     |
| Assembly arrangement  | Basic element with complete housing |

|                     |                |
|---------------------|----------------|
| <b>Connectivity</b> |                |
| Mounting type       | Screw mounting |

|                                |   |
|--------------------------------|---|
| <b>Controls and indicators</b> |   |
| Number of buttons              | 3 |

|                   |            |
|-------------------|------------|
| <b>Dimensions</b> |            |
| Dimensions        | 86 x 86 mm |
| Built-in depth    | 0 mm       |

|                         |      |
|-------------------------|------|
| <b>Electric current</b> |      |
| Rated current           | 10 A |

|                   |                                            |
|-------------------|--------------------------------------------|
| <b>Texts</b>      |                                            |
| Installation mode | For flush-mounted and hollow wall mounting |
| Lighting          | Without lighting (cannot be illuminated)   |
| Push button       | No                                         |
| Imprint           | With clear terminal markings               |

|                       |     |
|-----------------------|-----|
| <b>Sustainability</b> |     |
| REACH-SVHC free       | Yes |
| RoHS conform          | Yes |