



WPPS12BKO

10AX 1 Gang 2 Way Wall Switch & Back Box with Knockouts

Technical Features

Electric current	
Switching current	10 A

Installation, mounting	
Mounting on	Flush mounting

Voltage	
Rated voltage	250 V

Materials	
Colour	Grey
Surface finish	Glossy
Material	Steel
Treatment	Epoxy

Identification	
Assembly arrangement	Basic element with complete housing

Connectivity	
Mounting type	Screw mounting

Controls and indicators	
Number of buttons	1

Dimensions	
Dimensions	86 x 86 mm
Built-in depth	0 mm

Electric current	
Rated current	10 A

Texts	
Installation mode	For flush-mounted and hollow wall mounting
Lighting	Without lighting (cannot be illuminated)
Push button	No
Imprint	With clear terminal markings

Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes