



WNC001

cubyko 2-way switch wall mounted grey IP55

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Grey
RAL code	7011
Surface finish	Matt Satin finish
Material	Polypropylene (PP)

Identification

Assembly arrangement	Complete installation with frame
----------------------	----------------------------------

Accessories

Has labelling field	No
---------------------	----

Connectivity

Mounting type	Screw mounting
---------------	----------------

Controls and indicators

Number of buttons	1
-------------------	---

Dimensions

Dimensions	75 x 75 mm
Built-in depth	65 mm

Safety

Impact resistance IK	IK08
----------------------	------

Electric current

Rated current I _N	10 A
------------------------------	------

Connection

Type of contacts	2-way
------------------	-------

Texts

Type of connection	With plug-in terminals
--------------------	------------------------

Architecture

Control/operation element	Switch
---------------------------	--------

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes