



VE18PN

Enclosure,vector,IP65,18M,UV stable,with metric cable entry

Technical Features

Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	Yes
----------------------------	-----

Mounting on	Surface mounting
-------------	------------------

Electric current

Rated current IN	63 A
------------------	------

Equipment

Number of rails	1
-----------------	---

Number of rows	1
----------------	---

Number of section in width	1
----------------------------	---

With lock	No
-----------	----

Capacity

Number of modules	18
-------------------	----

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	302 mm
--------	--------

Width	418 mm
-------	--------

Depth	151 mm
-------	--------

Cover, door

Number of cabinet doors	1
-------------------------	---

Number of locks	0
-----------------	---

Dimensions

Number of width units	18
-----------------------	----

Cover, door

Door/cover is transparent	Yes
---------------------------	-----

Cabinet door type	Single door
-------------------	-------------

Connection

Number of conduit inlets	15
--------------------------	----

Materials

Material	Plastic
----------	---------

RAL code	7035
----------	------

Colour	Light grey
--------	------------

Equipment

Has mounting plate	No
--------------------	----

Materials

Ultraviolet-resistant	Yes
-----------------------	-----

Safety

Protection class	Isolation class II
------------------	--------------------

Ingress Protection (IP) class	IP65
-------------------------------	------

Locking type	Snap on lock Without lock
--------------	------------------------------

Glow wire test	850 °C
----------------	--------

Protection class with door	IP65
----------------------------	------

Sustainability	
RoHS conform	Yes