



VE110PN

Enclosure,vector,IP65,10M, UV stable, with metric cable entry

### Technical Features

#### Voltage

|                 |             |
|-----------------|-------------|
| Nominal voltage | 400 - 400 V |
|-----------------|-------------|

#### Installation, mounting

|                            |                  |
|----------------------------|------------------|
| Suitable for outdoor usage | Yes              |
| Mounting on                | Surface mounting |

#### Electric current

|                  |      |
|------------------|------|
| Rated current IN | 63 A |
|------------------|------|

#### Equipment

|                            |    |
|----------------------------|----|
| Number of rails            | 1  |
| Number of rows             | 1  |
| Number of section in width | 1  |
| With lock                  | No |

#### Capacity

|                   |    |
|-------------------|----|
| Number of modules | 10 |
|-------------------|----|

#### Functions

|                     |     |
|---------------------|-----|
| With conduit inlets | Yes |
|---------------------|-----|

#### Dimensions

|        |        |
|--------|--------|
| Height | 210 mm |
| Width  | 237 mm |
| Depth  | 114 mm |

#### Cover, door

|                         |   |
|-------------------------|---|
| Number of cabinet doors | 1 |
| Number of locks         | 0 |

#### Dimensions

|                       |    |
|-----------------------|----|
| Number of width units | 10 |
|-----------------------|----|

#### Cover, door

|                           |             |
|---------------------------|-------------|
| Door/cover is transparent | Yes         |
| Cabinet door type         | Single door |

#### Connection

|                          |   |
|--------------------------|---|
| Number of conduit inlets | 6 |
|--------------------------|---|

#### Materials

|          |            |
|----------|------------|
| Material | Plastic    |
| RAL code | 7035       |
| Colour   | Light grey |

#### Equipment

|                    |    |
|--------------------|----|
| Has mounting plate | No |
|--------------------|----|

#### Materials

|                       |     |
|-----------------------|-----|
| Ultraviolet-resistant | Yes |
|-----------------------|-----|

#### Safety

|                               |                              |
|-------------------------------|------------------------------|
| Protection class              | Isolation class II           |
| Impact resistance IK          | IK07                         |
| Ingress Protection (IP) class | IP65                         |
| Locking type                  | Snap on lock<br>Without lock |
| Glow wire test                | 850 °C                       |
| Protection class with door    | IP65                         |

---

**Sustainability**

---

RoHS conform

Yes

---