



JPE3618S25DS1

DB, elite, 36/18Pole, 250A ISO-DIN-SS, 1400x600x250mm

Technical Features

Connection

Number of accessible phases	54
-----------------------------	----

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Electric current

Rated current	250 A
---------------	-------

Equipment

With lock	Yes
Has mounting plate	No
Equipped with switch	Isolator
Number of switches	1
Type of busbar chassis	Split chassis

Capacity

Number of modules	42
-------------------	----

Weight

Weight	66 kg
--------	-------

Dimensions

Height	1400 mm
Width	600 mm
Depth	250 mm

Cover, door

Door/cover is transparent	No
---------------------------	----

Materials

Material	Stainless steel
Colour	Stainless steel

Safety

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP66
Locking type	3-point lever Key lock

Architecture

Number of poles	54
-----------------	----

Sustainability

RoHS conform	Yes
--------------	-----