



TRM693G



Module 1 flush mounted output 3A 230V + 2 inputs mains powered, KNX radio

Technical Features

Connectivity

Radio protocol	KNX Radio
----------------	-----------

Settings

Supported configuration mode	ETS easy quicklink
------------------------------	--------------------------

Connectivity

Receiver category	2
With bus system KNX	No
With bus system KNX radio	Yes

Dimensions

Dimensions	40 x 40 mm
Height	40 mm
Width	40 mm
Depth	20 mm
Built-in depth	40 mm

Electric current

Max. switching current	3 A
Rated current IN	3 A

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Materials

Colour	Light grey
--------	------------

Equipment

Radio frequency bidirectional	Yes
With switch for manual switch	Yes

Frequency

Frequency	50 - 50 Hz
Radio reception frequency	868.30 - 868.30 MHz

Power

Output power	690 W
230 V incandescent and halogen lamp	500 W
Power incandescent lamp	500 - 500 W

Voltage

Operating voltage	230 - 230 V
Rated operational voltage Ue	230 - 230 V
System supply voltage	230 V AC

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Operating temperature	-10 - 50 °C
-----------------------	-------------

Connection

Cross-section rigid conductor	0.5 - 2.5 mm²
Cross-section flexible conductor	0.5 - 1.5 mm²

Texts

Function	Easy additional functions: +6 scenes Repeat function can be activated to increase the radio range Reset function (to factory setting)
----------	---

Texts	
Installation mode	For installation behind flush-mounted inserts
Type of connection	With screw-in lift terminals
Sustainability	
RoHS conform	Yes