



L12801

Fuse carrier 1P+N 32A 400V 1M

Technical Features

Dimensions

Height	77 mm
Width	17.50 mm
Depth	75 mm

Architecture

Number of poles	2
Type of pole	1P+N

Electric current

Rated current	32 A
Rated current of fuse cartridge	32 A

Capacity

Number of modules	1
-------------------	---

Use conditions

Operating temperature	-5 - 40 °C
-----------------------	------------

Installation, mounting

Nominal tightening torque	1.80 - 1.80 Nm
Mounting on	DIN rail

Power

Total power loss under IN	1.50 W
---------------------------	--------

Voltage

Type voltage supply	AC
---------------------	----

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Connection

Cross-section of input and output with screws, for flexible conductors	10 - 10 mm ²
Cross-section of input and output with screws, for massive conductors	16 - 16 mm ²

Fuse

Fuse size	10 x 38
-----------	---------

Cover, door

Interlockable	No
---------------	----

Sustainability

RoHS conform	Yes
--------------	-----

Illustrations | Drawings

