



SL200552D4

Recy30% Trunking lid SL20055 cherry

Technical Features

Dimensions

Height	55 mm
Width	20 mm
Length	2000 mm

Materials

Material	Polyvinylchloride (PVC)
Colour	Cherry
Treatment	Foiled

Cover, door

Lid with soft lip	Without soft lip
-------------------	------------------

Equipment

With carpet border	No
With protective film	Yes

Safety

Ingress Protection (IP) class	IP40
Impact resistance IK	IK07

Use conditions

Operating temperature	5 - 60 °C
-----------------------	-----------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

