



JAB406S-IP65

Technical Features

Electric current

Rated current	63 A
Rated short-time withstand current I _{cw} 1s IEC 60947	1.5 kA

Use conditions

Operating temperature	-5 - +40 °C
-----------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated insulation voltage U _i	800 V
Rated impulse withstand voltage U _{imp}	8 V

Safety

Ingress Protection (IP) class	IP65
-------------------------------	------

Dimensions

Height	300 mm
Width	300 mm
Depth	200 mm

Installation, mounting

Mounting on	Wall mounting
-------------	---------------

Sustainability

REACH-SVHC free	Yes
-----------------	-----