10AX 2 Gang 1 Way Wall Switch

Technical Features

Electric current	
Switching current	10 A
Installation, mounting	
Mounting on	Flush mounting
Voltage	
Rated voltage	250 V
Frequency	
Frequency	50 - 60 Hz
Materials	
Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated
Identification	
Assembly arrangement	Basic element with full cover plate
Connectivity	
Mounting type	Screw mounting
Controls and indicators	
Number of buttons	2
Dimensions	
Dimensions	86 x 86 mm
Built-in depth	12 mm
Electric current	
Rated current IN	10 A
Texts	
Installation mode	For flush-mounted and hollow wall mounting
Lighting	Without lighting (cannot be illuminated)
Push button	No
Imprint	With clear terminal markings
Architecture	
Control/operation element	Double rocker
Sustainability	
REACh-SVHC free	Yes
RoHS conform	Yes