Product Datasheet
EV106



EV106

IP20

1-10V

Remote control dimmer 1-10V

Technical Features

Voltage	
Operating voltage	230 - 230 V
Frequency	
Frequency	50 - 50 Hz
Connectivity	
Dimming DALI	No
Power	
Power consumption during operation	3 VA
Power consumption standby	1 W
Use conditions	
Operating temperature	-10 - 45 °C
Dimensions	
Height	85 mm
Width	71 mm
Depth	65 mm
Connection	
Cross-section rigid conductor	1.5 - 10 mm^2
Cross-section flexible conductor	1 - 6 mm^2
Capacity	
Number of modules	4
Electric current	
Control current 1-10 V slave	50 mA
Materials	
Colour	Grey
Texts	
Type of connection	With screw terminals
Installation mode	For mounting on DIN rail
Junction	Connection for illuminated (max. 5 mA) or standard push-buttons