Product Datasheet
EV106



EV106

IP20

Remote control dimmer 1-10V

Technical Features

Voltage

Operating voltage	230 - 230 V

Frequency

Frequency	50 - 50 Hz

Connectivity

Dimming DALI	No

Power

Power consumption during operation	3 VA
Power consumption standby	1 W

Use conditions

Operating temperature	-10 - 45 °C

Dimensions

Height	85 mm
Width	71 mm
Depth	65 mm

Connection

Cross-section rigid conductor	1.5 - 10 mm^2
Cross-section flexible conductor	1 - 6 mm^2

Capacity

Number of modules	4

Electric current

Control current 1-10 V slave	50 mA

Materials

Colour	Grey

Texts

Type of connection	With screw terminals
Installation mode	For mounting on DIN rail
Junction	Connection for illuminated (max. 5 mA) or standard push-buttons