Product Datasheet
FK133



FK130

Steel enclosure, FK, plain door 2100x1000x400 mm

Technical Features

Dimensions	
Height	2100 mm
Width	1000 mm
Depth	400 mm
Thickness of sidewall	1.20 mm

Safety	
Ingress Protection (IP) class	IP65
Protection class	Isolation class I
Locking type	Key lock
Impact resistance IK	IK10

Equipment	
Number of flange plate openings	2

Installation, mounting	
Mounting on	Floor mounting
Suitable for outdoor usage	No

Materials	
Colour	Light grey
RAL code	7035
Treatment	Powder coated
Material	Metal

Cover, door	
Number of cabinet doors	1
Door/cover is transparent	No
Cabinet door type	Single door

Sustainability	
RoHS conform	Yes