Product Datasheet
FK114



FK114

Steel enclosure, FK, plain door 2100x600x500 mm

Technical Features

Dimensions

Height	2100 mm
Width	600 mm
Depth	500 mm
Thickness of sidewall	1.20 mm

Safety

Ingress Protection (IP) class	IP65
Protection class	Isolation class I
Locking type	Key lock
Impact resistance IK	IK10

Equipment

Number of flange plate openings	2

Installation, mounting

Mounting on	Floor mounting
Suitable for outdoor usage	No

Materials

Colour	Light grey
RAL code	7035
Treatment	Powder coated
Material	Metal

Cover, door

Number of cabinet doors	1
Door/cover is transparent	No
Cabinet door type	Single door

Sustainability

RoHS conform	Yes