Product Datasheet
TRE530



TRE530

Motion detector IR solar, radio, IP55, surface mounted, white

Technical Features

Dimensions

Installation height	4 - 4 m
Recommended installation height	2.50 - 2.50 m

Settings

Supported configuration mode	ETS easy quicklink
Minimal duty cycle	30 s

Functions

Maximal duty cycle	15 min

Connectivity

With bus system KNX radio	Yes

Scope of delivery

Bus connection included	Yes

Lighting

Response brightness adjustable	5 - 1000 lx

Detection

Detection angle	220 - 220
Detection angle horizontal	220 - 220

Use conditions

Operating temperature	-20 - 55 °C

Materials

Material	Acrylonitrile-Butadiene-Styrene (ABS) Polycarbonate (PC)

Texts

Function	Easy additional functions: +6 scenes, on/off operating mode, scene call-up upon motion/no motion Reset function (to factory setting)
Installation mode	For wall and ceiling mounting, corner installation with adapter

Reach distance

Max. transmission range frontally	16 m
Max. transmission range sideways	10 m