Product Datasheet
VMLF112SPD

VMLF710CU

12 way 100A Switch Type 2 SPD

Technical Features

Installation, mounting	
Mounting on	Flush mounting
Architecture	
Number of poles	2
Functions	
Overvoltage protection	Yes
Installation, mounting	
Suitable for outdoor usage	No
Capacity	
Number of modules	12
Electric current	
Rated current	100 A
Dimensions	
Depth	104 mm
Height	282 mm
Width	407 mm
Thickness of sidewall	1 mm
Cover, door	
Interlockable	No
Door/cover is transparent	No
Materials	
RAL code	9010
Colour	Pure white
Material	Steel
Connection	
Number of accessible phases	1
Equipment	
Number of rows	1
Number of rails	1
Extension possible	No
Safety	
Impact resistance IK	IK05
Ingress Protection (IP) class	IP2XC