Product Datasheet
VE106PN

VE106PN

Enclocure,vector,flush mounted,IP65,6M,UV stable,with metric cable entry

Technical Features

Voltage	
Nominal voltage	400 - 400 V
Rated operational voltage in DC	1000 - 1000 V
Installation, mounting	
Suitable for outdoor usage	Yes
Mounting on	Surface mounting
Electric current	
Rated current	63 A
Equipment	
Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	No
Capacity	
Number of modules	6
Functions	
With conduit inlets	Yes
Dimensions	
Height	190 mm
Width	165 mm
Depth	113 mm
Cover, door	
Number of cabinet doors	1
Number of locks	0
Dimensions	
Number of width units	6
Cover, door	
Door/cover is transparent	Yes
Connection	
Number of conduit inlets	3
Connectivity	
Mounting type	Screw mounting
Materials	
Material	Polycarbonate (PC)
RAL code	7035
Colour	Light grey
Equipment	
Has earthing terminal block	No
Has mounting plate	No
Materials	
Ultraviolet-resistant	Yes
Safety	
Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP65

Safety	
Locking type	Snap on lock Without lock
Glow wire test	850 °C

Sustainability	
RoHS conform	Yes