JG220U

IP66 40A 2P UTILITY ISOLATOR

Technical Features

Architecture	
Number of poles	2
Type of pole	1P+N
Electric current	
Rated current	40 A
Acceptable current rating AC21 category A	40 A
Acceptable current rating AC22 category A	40 A
Voltage	
Rated operational voltage Ue	250 - 250 V
Electric current	
Rated short-circuit making capacity Icm under 240 V AC according to IEC 60947-3	0.48 kA
Voltage	
Rated insulation voltage Ui	250 V
Electric current	
Rated short-time withstand current Icw t=1s 220 - 240 V AC according to IEC 60947 - 3	0.48 kA
Installation, mounting	
Nominal tightening torque	2.50 - 2.50 Nm
Dimensions	
Height	170 mm
Width	84 mm
Depth	87 mm
Safety	
Ingress Protection (IP) class	IP66
Use conditions	
Operating temperature	-5 - 40 °C
Connection	
Cross-section rigid conductor	6 - 10 mm^2
Frequency	
Frequency	50 - 60 Hz
Sustainability	
RoHS conform	Yes