Product Datasheet
VF112PF

VF112PF3

Small distributor,golf,flush,1row,12M,IP40,MS-terminal,PE,white door

Technical Features

Voltage	
Nominal voltage	400 - 400 V
Installation, mounting	
Suitable for outdoor usage	No
Mounting on	Flush mounting
Electric current	
Rated current	63 A
Equipment	
Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	No
Capacity	
Number of modules	12
Functions	
Has protection main switch	No
With conduit inlets	Yes
Scope of delivery	
Number of RCCB in enclosure	0
Dimensions	
Height	293 mm
Width	352 mm
Depth	97.50 mm
Built-in height	257 mm
Built-in width	318 mm
Cover, door	
Number of cabinet doors	1
Dimensions	
Built-in depth	72 mm
Cover, door	
Number of locks	0
Dimensions	
Number of width units	12
Cover, door	
Door/cover is transparent	No
Materials	
Material	Plastic
RAL code	9010
Colour	Pure white
Equipment	
Has earthing terminal block	Yes
Has mounting plate	No
Materials	
Ultraviolet-resistant	No

Safety	
Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP40
Locking type	Snap on lock Without lock
Glow wire test	650 °C

Sustainability	
RoHS conform	Yes