

- (GB) 4 RJ45 connectors
cat. 5e UTP
- (DE) 4 Steckverbinder RJ45
cat. 5e UTP
- (SE) 4 RJ45 kontaktdon
cat. 5e UTP

User instructions

Bedienungsanleitung

Bruksanvisning

6T 6185.b

TN004

(GB)

Product scope

TN004 is a RJ45 connector to be installed in a wall mounting equipment supporting unit or communication box.

Technical specifications

- Product complies with Standard: EN 60603-7-5.
- **CE** Conformity
- Self-stripping contacts (no tool required).
- Standard Colour Code: EIA/TIA 568 A & B.
- Connector RJ45, Category 5e UTP.

(DE)

Produktbeschreibung

Der TN004 ist ein RJ45-Anschluss für die Montage in einer Wandtafel bzw. einem Datenübertragungsschrank

Technische Spezifikationen

- Entspricht der Norm: EN 60603-7-5.
- **CE** Konformität
- Selbstschneidende Kontakte (kein Werkzeug erforderlich).
- Norm-Farbencode: EIA/TIA 568 A & B.
- Steckverbinder RJ45, Kategorie 5e UTP.

(SE)

Presentation av produkten

TN004 är ett RJ45 kontaktdon avsett för montering i en väggållare för utrustning eller apparatdosa.

Tekniska data

- Uppfyller norm: EN 60603-7-5.
- **CE** Märkt
- Kontaktarna är självavskalande (utan verktyg).
- Standardiserad färgkod: EIA/TIA 568 A & B.
- RJ45 Kontaktdon, Kategori 5e UTP.

Installation - Montage - Montage


①

② Cable Category 5e UTP
Kabel Kategorie 5e UTP
Kabel av kategori 5e UTP


③

④

⑤



Connector removal - Demontage des Anschlusses - Kontaktdonets demontering



Warranty (GB)

A warranty period of 24 months is offered on hager products, from date of manufacture, relating to any material of manufacturing defect. If any product is found to be defective it must be returned via the installer and supplier (wholesaler). The warranty is withdrawn if:

- after inspection by hager quality control dept the device is found to have been installed in a manner which is contrary to IEE wiring regulations and accepted practice within the industry at the time of installation.
- the procedure for the return of goods has not been followed.

Explanation of defect must be included when returning goods.

Garantie (DE)

Es gelten die Allgemeinen Geschäftsbedingungen der Hager Electro GmbH. bzw. die gesetzliche Regelung.

Garanti (SE)

24 månader på alla material- eller fabriktionsfel, räknat från deras tillverkningsdatum. Vid bristfällighet ska produkten återlämnas till kundens grossist. Garantin gäller endast om återlämningsförfarandet via installatören och grossisten följs och om vår kvalitetskontrollavdelning har undersökt produkten och inte upptäckt något fel som uppkommit till följd av ett verkställande och/eller en användning som strider mot konstens alla regler. Eventuella anmärkningar som beskriver bristfälligheten ska medfölja produkten.

Hager 11.2009