Product Datasheet
75664590

75664590

B.IQ push-button 4gang thermostat, display, KNX - B.IQ, glass p. white

Technical Features

Installation, mounting

Mounting on	Flush mounting

Use conditions

Operating temperature	-5 - 45 °C

Functions

With room temperature controller	Yes

Dimensions

Height	149.20 mm
Width	88.50 mm
Depth	16.65 mm

Equipment

Number of actuation points	10

Controls and indicators

With LED indication	Yes

Materials

Colour	Polar white
RAL code	9010
Material	Glass
Surface finish	Glossy

Accessories

Has labelling field	No

Screen

With display	Yes

Texts

Function	For switch, push-button, dimmer, blind and thermostat functions With valve protection function Button help function can be activated
Operating mode	Controller operating modes: comfort, standby, night and frost/heat protection mode
Protection	With dismantling protection
Temperature	Temperature measurement via internal Temperature sensor and/or external communication object (weighting ratio parameterisable) Provision of the internal temperature value via communication object

Sustainability

REACh-SVHC free	Yes
RoHS conform	Yes