Product Datasheet
VE112PN

VE112PN

Enclosure,vector,surface mounted,IP65,1x12M,UV stable, with metric cable entry

Technical Features

Voltage	
Nominal voltage	400 - 400 V
Rated operational voltage in DC	1000 - 1000 V
Installation, mounting	
Suitable for outdoor usage	Yes
Mounting on	Surface mounting
Electric current	
Rated current	63 A
Equipment	
Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	No
Capacity	
Number of modules	12
Functions	
With conduit inlets	Yes
Dimensions	
Height	302 mm
Width	310 mm
Depth	151 mm
Cover, door	
Number of cabinet doors	1
Number of locks	0
Dimensions	
Number of width units	12
Cover, door	
Door/cover is transparent	Yes
Connection	
Number of conduit inlets	12
Connectivity	
Mounting type	Screw mounting
Materials	
Material	Polycarbonate (PC)
RAL code	7035
Colour	Light grey
Equipment	
Has earthing terminal block	No
Has mounting plate	No
Materials	
Ultraviolet-resistant	Yes
Safety	
Protection class	Isolation class II
Impact resistance IK	IK08
Ingress Protection (IP) class	IP65

Safety	
Locking type	Snap on lock Without lock
Glow wire test	850 °C

Sustainability	
RoHS conform	Yes