

UKCA DECLARATION OF CONFORMITY No. UKCA 23.2928.08.23

We **Hager Electro SAS**
BP3
67215 OBERNAI CEDEX - FRANCE

Declare that the product(s)

Designation

Plate Switches 250V 50Hz 10AX

Type reference(s)

White Moulded & Decorative Range

Trademark

Hager

is (are) in conformity with the relevant United Kingdom legislation:

- SI 2012/3032 Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012 (as amended)
 - SI 2016/1091 Electromagnetic Compatibility (EMC) Regulations 2016 (as amended)
 - SI 2016/1101 Electrical Equipment (safety) Regulations 2016 (as amended)
-
-

Standard(s) and/or relevant document(s) to which conformity is declared

Standard number + relevant amendments together with the edition dates

BS EN 60669-1:2018

BS EN IEC 63000:2018

If applicable, mention here for radio products, the data about notified body. See RE legislation - Annex VI - point 7

This declaration of conformity is issued under the sole responsibility of the manufacturer.

On behalf of Hager Electro SAS

Name of signatory

Eddie Li

Function of signatory

Lab Manager - Group Quality & Environment

Place and date of issue

Huizhou, CN 09/08/2023

Signature



UKCA DECLARATION OF CONFORMITY

No. UKCA 23.2928.08.23

Type references

White Moulded Plate Switches

Product Reference	Product Description
WMPS11	10AX 1GANG 1WAY WALL SWITCH
WMPS11/FAN	10AX 1GANG 1WAY WALL SWITCH MARKED 'FAN'
WMPS21	10AX 2 GANG 1WAY WALL SWITCH
WMPS21-ME	10AX 2 GANG 1WAY WALL SWITCH
WMPS21-NM	10AX 2 GANG 1WAY WALL SWITCH
WMPS12	10AX 1 GANG 2 WAY WALL SWITCH
WMPS12R	10AX1 GANG 2 WAY RETRACTIVE PLATE SWITCH
WMPS12RB	10AX1 GANG 2 WAY RETRACTIVE PLATE SWITCH WITH BELL MARK
WMPS12RW	10AX1 GANG 2 WAY RETRACTIVE PLATE SWITCH WITH BELL MARK
WMPS12RWG	10AX1 GANG 2 WAY RETRACTIVE PLATE SWITCH-WIDER ROCKER
WMPS12RWG/FB	10AX1 GANG 2 WAY RETRACTIVE PLATE SWITCH WITH 'FAN BOOST'
WMPS12W	10AX 1G 2W WALL SWITCH WIDE ROCKER
WMPS12WG	10AX 1G/2W SWITCH WIDE ROCKER GREY
WMPS16	10AX 1 GANG INTERMEDIATE PLATE SWITCH
WMPS16W	10AX 1 GANG INTERMEDIATE PLATE SWITCH WIDER ROCKER
WMPS16WG	10AX 1 GANG INTERMEDIATE PLATE SWITCH WIDER ROCKER GREY
WMPS22	10AX 2G 2W WALL SWITCH
WMPS22W	10AX 2G 2W WALL SWITCH WIDE ROCKER
WMPS22WG	10AX 2G 2W WALL SWITCH WIDE ROCKER GREY
WMPS32	10AX 3G 2W WALL SWITCH
WMPS42	10AX 4G 2W WALL SWITCH
WMPS262	10AX 2G 2W & INT WALL SWITCH
WMPS62	10AX 6G 2W WALL SWITCH

UKCA DECLARATION OF CONFORMITY

No. UKCA 23.2928.08.23

Type references

Decorative Plate Switches – Flat

Product Reference	Product Description
WFPS12BNB	10AX 1G 2WAY SW BRUSHED STEEL BLACK
WFPS12BSB-A	10AX 1G 2WAY SW BRUSHED STEEL BLACK
WFPS12BSB	10AX 1G 2WAY SW BRUSHED STEEL BLACK
WFPS12BSW-A	10AX 1G 2WAY SWITCH BRUSHED STEEL WHITE
WFPS12BSW	10AX 1G 2WAY SWITCH BRUSHED STEEL WHITE
WFPS12PBB	10AX 1G 2 WAY WALL SW POLISHED BRASS BK
WFPS12PBW	10AX 1G 2 WAY WALL SW POLISHED BRASS WHITE
WFPS12PSB	10AX 1G 2WAY SW POLISHED STEEL BLACK
WFPS12PSW	10AX 1G 2WAY SW POLISHED STEEL WHITE
WFPS12BSP	10AX Wall Switch Flat Plate 10AX 1 Gang 2 Way
WFPS12WBSW-A	10AX 1G 2W SW W/R BRUSHED STEEL WHITE
WFPS12WPSW	10AX Wall Switch Flat Plate 10AX 1 Gang 2 Way
WFPS12WPBW	10AX Wall Switch Flat Plate 10AX 1 Gang 2 Way
WFPS12WPSB	10AX Wall Switch Flat Plate 10AX 1 Gang 2 Way
WFPS12WBSP	10AX Wall Switch Flat Plate 10AX 1 Gang 2 Way
WFPS12WPBB	10AX Wall Switch Flat Plate 10AX 1 Gang 2 Way
WFPS12WBNB	10AX Wall Switch Flat Plate 10AX 1 Gang 2 Way
WFPS12WBSB	10AX Wall Switch Flat Plate 10AX 1 Gang 2 Way
WFPS12WBSW	10AX Wall Switch Flat Plate 10AX 1 Gang 2 Way
WFPS16BNB	10AX INTERMEDIATE SWITCH BLACK NICKEL BLACK
WFPS16PSW	10AX Intermediate Switch Flat Plate
WFPS16PBW	10AX Intermediate Switch Flat Plate
WFPS16PSB	10AX Intermediate Switch Flat Plate
WFPS16BSW	10AX Intermediate Switch Flat Plate
WFPS16BSP	10AX Intermediate Switch Flat Plate
WFPS16BSB	10AX Intermediate Switch Flat Plate
WFPS16PBB	10AX Intermediate Switch Flat Plate
WFPS16BSB-A	10AX INTERMEDIATE SWITCH BLACK NICKEL BLACK
WFPS16BSW-A	10AX INTERMEDIATE SWITCH BRUSHED STEEL WHITE
WFPS22PBW	10AX 2 G 2 WAY WALL SW POLISHED BRASS WH
WFPS22PBB	10AX Wall Switch Flat Plate 10AX 2 Gang 2 Way
WFPS22BSB	10AX Wall Switch Flat Plate 10AX 2 Gang 2 Way
WFPS22BSW	10AX Wall Switch Flat Plate 10AX 2 Gang 2 Way
WFPS22BSP	10AX Wall Switch Flat Plate 10AX 2 Gang 2 Way
WFPS22BSB-A	10AX 2G 2WAY SWITCH BRUSHED STEEL BLACK
WFPS22BNB	10AX 2 G 2 WAY WALL SW BLACK NICKEL BK
WFPS22BSW-A	10AX 2G 2WAY SW BRUSHED STEEL WHITE
WFPS22PSB	10AX 2G 2WAY SW POLISHED STEEL BLACK
WFPS22PSW	10AX 2G 2WAY SW BRUSHED STEEL WHITE

UKCA DECLARATION OF CONFORMITY

No. UKCA 23.2928.08.23

Type references

Decorative Plate Switches – Flat (cont)

Product Reference	Product Description
WFPS22WBSB	10AX2G 2W WALL SW W/R BLACK NICKEL BK
WFPS22WBNB	10AX2G 2W WALL SW W/R BLACK NICKEL BK
WFPS22WBSW-A	10AX 2G 2W WALL SW W/R BRUSHED STEEL WH
WFPS22WPSW	10AX Wall Switch Flat Plate 10AX 2 Gang 2 Way
WFPS22WBSW	10AX Wall Switch Flat Plate 10AX 2 Gang 2 Way
WFPS22WPBW	10AX Wall Switch Flat Plate 10AX 2 Gang 2 Way
WFPS22WPSB	10AX Wall Switch Flat Plate 10AX 2 Gang 2 Way
WFPS22WBSP	10AX Wall Switch Flat Plate 10AX 2 Gang 2 Way
WFPS22WPBB	10AX2G 2W WALL SW W/R POLISHED BRASS BK
WFPS32PBW	10AX Wall Switch Flat Plate 10AX 3 Gang 2 Way
WFPS32BNB	10AX 3 G 2 WAY WALL SW BLACK NICKEL BK
WFPS32BSW	10AX 3G 2WAY SWITCH BRUSHED STEEL WHITE
WFPS32BSB	10AX 3 G 2 WAY WALL SW BLACK NICKEL BK
WFPS32BSB-A	10AX 3G 2WAY SWITCH BRUSHED STEEL BLACK
WFPS32BSW-A	10AX 3G 2WAY SWITCH BRUSHED STEEL WHITE
WFPS32BSP	10AX Wall Switch Flat Plate 10AX 3 Gang 2 Way
WFPS32PBB	10AX Wall Switch Flat Plate 10AX 3 Gang 2 Way
WFPS32PSB	10AX 3G 2WAY SWITCH POLISHED STEEL BLACK
WFPS32PSW	10AX 3G 2WAY SW POLISHED STEEL WHITE
WFPS42BNB	10AX 4 G 2 WAY WALL SW BLACK NICKEL BK
WFPS42PBW	10AX Wall Switch Flat Plate 10AX 4 Gang 2 Way
WFPS42BSW	10AX Wall Switch Flat Plate 10AX 4 Gang 2 Way
WFPS42BSB	10AX Wall Switch Flat Plate 10AX 4 Gang 2 Way
WFPS42BSB-A	10AX 4 G 2 WAY WALL SW BRUSHED STEEL BK
WFPS42BSW-A	10AX 4 G 2 WAY WALL SW BRUSHED STEEL WH
WFPS42BSP	10AX Wall Switch Flat Plate 10AX 4 Gang 2 Way
WFPS42PBB	10AX Wall Switch Flat Plate 10AX 4 Gang 2 Way
WFPS42PSB	10AX 4 G 2 WAY WALL SW POLISHED STEEL BK
WFPS42PSW	10AX 4 G 2 WAY WALL SW POLISHED STEEL WH

UKCA DECLARATION OF CONFORMITY

No. UKCA 23.2928.08.23

Type references

Decorative Plate Switches – Raised

Product Reference	Product Description
WRPS12BNB	10AX 1G 2 WAY WALL SW BLACK NICKEL BLACK
WRPS12BSB-A	10AX 1G 2WAY SW BRUSHED STEEL BLACK
WRPS12BSW-A	10AX 1G 2WAY SW BRUSHED STEEL WHITE
WRPS12PBB	10AX 1G 2 WAY WALL SW POLISHED BRASS BK
WRPS12PBW	10AX 1G 2 WAY WALL SW POLISHED BRASS WH
WRPS12PSB	10AX 1G 2WAY SW POLISHED STEEL BLACK
WRPS12PSW	10AX 1G 2WAY SW POLISHED STEEL WHITE
WRPS12BSB	10AX 1G 2WAY SW POLISHED STEEL
WRPS12BSW	10AX 1G 2WAY SW POLISHED STEEL
WRPS12BSP	Wall Switch Raised Plate 10AX 1 Gang 2 Way
WRPS12WBSB-A	10AX 1G 2WAY SW W/R BRUSHED STEEL BLACK
WRPS12WBSW-A	10AX 1G 2WAY SW W/R BRUSHED STEEL WHITE
WRPS12WPBW	10AX1G 2W WALL SW W/R POLISHED BRASS WH
WRPS12WBSB	10AX1G 2W WALL SW W/R POLISHED BRASS WH
WRPS12WPSW	10AX 1G 2W SW W/R POLISHED STEEL WHITE
WRPS12WBSW	10AX 1G 2W SW W/R POLISHED STEEL WHITE
WRPS16	10AX INTERMEDIATE SWITCH
WRPS16BNB	10AX INTERMEDIATE SWITCH BLACK NICKEL BLACK
WRPS16BSP	10AX Intermediate Switch Raised Plate
WRPS16BSB-A	10AX INTERMEDIATE SWITCH BRUSHED STEEL BLACK
WRPS16BSW-A	10AX INTERMEDIATE SWITCH BRUSHED STEEL WHITE
WRPS16BSW	10AX INTERMEDIATE SWITCH BRUSHED STEEL WHITE
WRPS16BSB	10AX INTERMEDIATE SWITCH BRUSHED STEEL WHITE
WRPS16PBB	10AX INTERMEDIATE SWITCH POLISHED BRASS BLACK
WRPS16PBW	10AX INTERMEDIATE SWITCH POLISHED BRASS WHITE
WRPS16PSB	10AX INTERMEDIATE SWITCH POLISHED STEEL BLACK
WRPS16PSW	10AX INTERMEDIATE SWITCH POLISHED STEEL WHITE
WRPS22BNB	10AX 2 G 2 WAY WALL SW BLACK NICKEL BK
WRPS22BSW	Wall Switch Raised Plate 10AX 2 Gang 2 Way
WRPS22BSB	10AX 2G 2WAY SW BRUSHED STEEL BLACK
WRPS22WBSB	10AX2G 2W WALL SW W/R BRUSHED STEEL BK
WRPS22BSB-A	10AX 2G 2WAY SW BRUSHED STEEL BLACK
WRPS22BSW-A	10AX 2G 2WAY SW BRUSHED STEEL WHITE
WRPS22PBB	10AX 2 G 2 WAY WALL SW POLISHED BRASS BK
WRPS22PBW	10AX 2 G 2 WAY WALL SW POLISHED BRASS WH
WRPS22PSB	10AX 2G 2WAY SW POLISHED STEEL BLACK
WRPS22PSW	10AX 2G 2 WAY SW POLISHED STEEL WHITE
WRPS22WBNB	10AX2G 2W WALL SW W/R BLACK NICKEL BK
WRPS22WBSB-A	10AX2G 2W WALL SW W/R BRUSHED STEEL BK

UKCA DECLARATION OF CONFORMITY

No. UKCA 23.2928.08.23

Type references

Decorative Plate Switches – Raised (cont)

Product Reference	Product Description
WRPS32BNB	10AX 3 G 2 WAY WALL SW BLACK NICKEL BK
WRPS32BSB-A	10AX 3G 2WAY SWITCH BRUSHED STEEL BLACK
WRPS32BSW-A	10AX 3G 2WAY SWITCH BRUSHED STEEL WHITE
WRPS32PBB	10AX 3 G 2 WAY WALL SW POLISHED BRASS BK
WRPS32PBW	10AX 3 G 2 WAY WALL SW POLISHED BRASS WH
WRPS32BSB	10AX 3 G 2 WAY WALL SW POLISHED BRASS WH
WRPS32BSP	10AX Wall Switch Raised Plate 3 Gang 2 Way
WRPS32BSW	10AX Wall Switch Raised Plate 3 Gang 2 Way
WRPS32PSB	10AX 3G 2WAY SW POLISHED STEEL BLACK
WRPS32PSW	10AX 3G 2WAY SW POLISHED STEEL WHITE
WRPS42BNB	10AX 4 G 2 WAY WALL SW BLACK NICKEL BK
WRPS42BSB-A	10AX 4 G 2 WAY WALL SW BRUSHED STEEL BK
WRPS42BSW-A	10AX 4 G2 WAY WALL SW BRUSHED STEEL WH
WRPS42PBB	10AX Wall Switch Raised Plate 4 Gang 2 Way
WRPS42BSP	10AX Wall Switch Raised Plate 4 Gang 2 Way
WRPS42BSB	10AX Wall Switch Raised Plate 4 Gang 2 Way
WRPS42BSW	10AX Wall Switch Raised Plate 4 Gang 2 Way
WRPS42PBW	10AX 4 G 2 WAY WALL SW POLISHED BRASS WH
WRPS42PSB	10AX 4 G 2 WAY WALL SW POLISHED STEEL BK
WRPS42PSW	10AX 4 G 2 WAY WALL SW POLISHED STEEL WH
WRPS22BSP	10AX 2 Gang 2 Way Wall Switch Raised Plate
WRPS32BSP	10AX 3 Gang 2 Way Wall Switch Raised Plate
WRPS42BSP	10AX 4 Gang 2 Way Wall Switch Raised Plate
WRPS42PBB	10AX 4 Gang 2 Way Wall Switch Raised Plate
WRPS12WPSB	10AX 1 Gang 2 Way Wall Switch Raised Plate
WRPS12WBSP	10AX 1 Gang 2 Way Wall Switch Raised Plate
WRPS12WPBB	10AX 1 Gang 2 Way Wall Switch Raised Plate
WRPS12WBNB	10AX 1 Gang 2 Way Wall Switch Raised Plate
WRPS22WPSW	10AX 2 Gang 2 Way Wall Switch Raised Plate
WRPS22WBSW	10AX 2 Gang 2 Way Wall Switch Raised Plate
WRPS22WPBW	10AX 2 Gang 2 Way Wall Switch Raised Plate
WRPS22WPSB	10AX 2 Gang 2 Way Wall Switch Raised Plate
WRPS22WBSP	10AX 2 Gang 2 Way Wall Switch Raised Plate
WRPS22WPBB	10AX 2 Gang 2 Way Wall Switch Raised Plate

UKCA DECLARATION OF CONFORMITY

No. UKCA 23.2928.08.23

Type references

Metalclad Plate Switches

Product Reference	Product Description
WPPS12	10AX 1 Gang 2 WAY RAISED PLATE SWITCH
WPPS12B	10AX 1 Gang 2 WAY RAISED PLATE SWITCH
WPPS12BKO	10AX 1 Gang 2 WAY RAISED PLATE SWITCH& BOX WO KOS
WPPS12BKOW	10AX 1 Gang 2 WAY RAISED PLATE SWITCH& Box CW KOS WHITE
WPPS12BW	10AX 1 Gang 2 WAY RAISED PLATE SWITCH& Box CW KOS WHIT
WPPS12RBW	10AX PUSH SWITCH WITHOUT KNOCKOUTS
WPPS12W	10AX 1G 2W WALL SWITCH WHITE
WPPS22	10AX 2G 2W WALL SWITCH
WPPS22B	10AX 2G 2W WALL SWITCH & BOX WO KOS
WPPS22BW	10AX 2 GANG 2 WAY WALL SWITCH WITHOUT KNOCKOUTS
WPPS22BKO	10AX 2G 2W WALL SWITCH & BOX WO KOS
WPPS22BKOW	10AX 2G 2W WALL SWITCH & BOX WO KOS WHITE
WPPS22W	10AX 2 Gang 2 WAY RAISED PLATE SWITCH – WIDE ROCKER
WPPS32	10AX 3G 2W WALL SWITCH
WPPS32BKO	10AX 3 Gang 2 WAY RAISED PLATE SWITCH& BOX WO KOS
WPPS32BKOW	10AX 3 Gang 2 WAY RAISED PLATE SWITCH& Box CW KOS WHITE
WPPS32W	10AX 3G 2W WALL SWITCH WHITE
WPPS32BW	10AX 3 Gang 2 Way Wall Switch Without Knockouts
WPPS12RW	10AX Push Switch Plate Only
WPPS12RBKOW	10AX Push Switch with Knockouts
WPPS2BKO	Grey 10AX 1 Gang 2 Way Wall Switch with Knockouts
WPPS32B	Grey 10AX 3 Gang 2 Way Wall Switch without Knockouts
WPPS12R	Grey 10AX Push Switch Plate Only
WPPS12RB	Grey 10AX Push Switch without Knockouts
WPPS12RBKO	Grey 10AX Push Switch with Knockouts
WPPS2BKO	Grey 10AX 1 Gang 2 Way Wall Switch with Knockouts

UKCA DECLARATION OF CONFORMITY

No. UKCA 23.2928.08.23

Evidence(s)

Documents listed below have been developed to assure that all essential requirements of applied directive(s) are fulfilled:

If the product is not in the scope of Radio Equipment directive, fulfil table 1a, if yes fulfil table.

Table 1a Risk Assessment for Equipment without Radio		Applicable: <input checked="" type="checkbox"/> Yes <input type="checkbox"/> No	
Only designated standards published on GOV.UK (https://www.gov.uk/guidance/designated-standards) are used:	Yes BS EN 60669-1:2018		
Scope and classification fully covers the product (case 1 of Hager Group risk analysis) :	Yes Designated after 2016		
Comments :	BS Standard updated in 2018		
Hager Group risk analysis: Only if there is at least one "No", then you have to explain how you cover the essential requirements and fill the document <u>DMS034433</u> - Hager Group risk analysis)	DMS034433 followed using case 1 of Hager Group method: Designated Standard Used		

Table 1b Risk Assessment for Radio equipment		Applicable: <input type="checkbox"/> Yes <input checked="" type="checkbox"/> No	
Hager Group risk assessment: Fill document DMS063155			

Evidence(s) / Evidence(s)

Documents listed below have been used in order to establish the conformity to the essential requirements of the relevant directives

Certificate(s) / test report(s):	Hager Group CNAS Test Report LB 20 0369 Nemko Certificate C11 41963 Nemko Certificate C15 47590
Mark approval(s):	None
Product documentation :	See Hager Website
Comments:	None

Signature (technical design)

Name of signatory

John Lee

Place and date of issue

Huizhou, CN 09/08/2023

Function of signatory

Business Development Manager

Signature



UKCA DECLARATION OF CONFORMITY

No. UKCA 23.2928.08.23

Designated Standards

Designated standard UKCA Electrical Equipment (Safety) Regulations 2016:

S.I. 2016 No. 1101	EN 60669-1:2018	Switches for household and similar fixed electrical installations - Part 1: General requirements	01/01/2021	0009/21
-----------------------	-----------------	--	------------	---------

Designated standard UKCA Electromagnetic Compatibility Regulations 2016:

S.I. 2016 No. 1101	EN 60669-1:2018	Switches for household and similar fixed electrical installations - Part 1: General requirements	01/01/2021	0007/21
-----------------------	-----------------	--	------------	---------

Designated standard UKCA RoHS:

S.I. 2012 No. 3033	EN IEC 63000:2018	Technical documentation for the assessment of electrical and electronic products with respect to the restriction of hazardous substances	01/01/2021	0037/21
-----------------------	-------------------	--	------------	---------