

Sollysta Decorative 2G Lounge Plate for TV, Power and Data with USB A+C

Designed for power and media requirements with the added benefits of USB charging in a compact and stylish design.

The Sollysta 2G Lounge Plate For TV, Power & Data includes an integrated twin port USB-A+C. The perfectly compact power and media plate allows for easy installation of essential media modules. Available in the Decorative Raised Brushed Steel in both white and black inserts.

The Euro Module aperture will accommodate up to 4 single modules (50mm x 25mm) or 2 double (50mm x 50mm) modules from the telephone and media module range. Sold separately is the exclusively compatible 47mm deep steel back box (WFTVBOX47H) for easy flush installation.

Sold separately is the exclusively compatible 47mm deep steel back box (WFTVBOX47H) for easy flush installation.



WRTVLPHBSW



WRTVLPHBSB




WFTVBOX47H

Description	Cat ref.
2G Lounge Plate For TV, Power & Data Raised Brushed Steel White	WRTVLPHBSW
2G Lounge Plate For TV, Power & Data Raised Brushed Steel Black	WRTVLPHBSB
Lounge Plate Back Box Half Height	WFTVBOX47H

Technical characteristics (Socket)

Standard	Socket complies with BS 1363-2
Nominal voltage rating	250V AC
Rated voltage rating	220-230 V AC
Current rating	13A per Socket Outlet
Switching	Double Pole Switching Mechanism
Number of USB Ports	2
USB Intelligent Connection	Yes
USB Output Power	15.5W
USB Output Voltage	5.0 V d.c.
USB Standby Power Consumption	≤0.15W
USB Overload Protection on Output	2.8±0.3A
Fixing mode	Screws 20mm & 30mm (included)
Material	Stainless Steel
IP Protection Index	IP20
Weight	348g (with screws)

Warranty - Hager undertakes to replace or repair at its discretion products should they become inoperable within the time periods as stated.



Dimensions

Catalogue Reference	A (mm)	B (mm)	C (mm)	D (mm)
WRTVLPHBSW	292	86	31.5	17.9
WRTVLPHBSB				

Note: For mounting lounge plate use the compatible back box **WFTVBOX47H**.

Euro Style Modules

Description	Mod Width	Cat ref. (White)	Cat ref. (Black)
BT Telephone Master Euromodule	1	WMMBTM	WMMBTMB
BT Telephone Secondary Euromodule	1	WMMBTS	WMMBTBSB
RJ11 - Modem Euromodule	1	WMMRJ11	WMMRJ11B
RJ45 - Cat 6 UTP Euromodule	1	WMMRJ45	WMMRJ45B
Phono Plugs - Red/Black - Gold Plated Euromodule	1	WMMPP	-
Speaker Terminal Posts - Gold Plated Euromodule	1	WMMSP	-
Single IEC Female Non Isolated Euromodule	1	WMMTVF	WMMTVFB
Single IEC Male Non Isolated Euromodule	1	WMMTVM	WMMTVMB
Single Satellite F Connector Euromodule	1	WMMSAT	WMMSATB
Single Blank Euromodule	1	WMMB	WMMBB
PIR Occupancy Sensor Euromodule 5m	1	WMMPIR05X	-
PIR Occupancy Sensor Euromodule 10m	1	WMMPIR10X	-
HDMI Module	2	WMMHDMI	WMMHDMIB
USB Euromodule with Twin USB	2	WMMUSB	WMMUSBB
Diplexer - TV & FM Radio Euromodule	2	WMMDX	WMMDXB
Triplexer - TV, Satellite & FM Radio Euromodule	2	WMMTX	WMMTXB
Quadplexer - TV, Satellite, FM Radio & Return Euromodule	2	WMMQX	WMMQXB