Product Datasheet
6765102089



6765102089

Soc.out. earth.pin+LED orient.,enhncd contact prot.,screw-in lift ,1930/R.cl,wh

Technical Features

Voltage

Rated voltage	250 V

Electric current

Rated current	16 A

Frequency

Frequency	50 - 60 Hz

Materials

Colour	Polar white
RAL code	9010
Surface finish	Glossy
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	71 mm
Width	71 mm
Depth	42 mm

Installation, mounting

Mounting on	Flush mounting

Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting Claw mounting

Equipment

Connector/plug type socket outlet	Earthing pin
Rotated central insert	No
With hinged lid	No
With round protective earth pin	Yes
With signal lamp	No
With lock	No

Accessories

Has labelling field	No

Capacity

Number of modules	1

Controls and indicators

Type of lighting for the installation devices	Integrated orientation light

Safety

With enhanced contact protection	Yes
Ingress Protection (IP) class	IP20

Functions

With orientation lighting	Yes
With function lighting	No

Identification

With imprint	No

Texts

Cover	Central cover plate
Lighting	Additional benefit by combination of a socket outlet with an orientation light

Texts

Wiring	Through-wiring possible, therefore also ideal for retrofitting
Protection	Enhanced contact protection
Type of connection	With screw-in lift terminals

Suitable for

R.x

Sustainability

Halogen free	Yes
RoHS conform	Yes