

IP66

**For the  
toughest  
environment**



**:hager**

# IP66

## Beautifully safe

With its rugged good look and ease of operation you can be sure that IP66 will provide protection for your wiring accessories in even the toughest of environment.

A host of innovative design solutions provide both installer and end user with a range of products that is easy to work with and retain their good looks whatever the environment throws at them.




### Advantages:

- IP66 complete protection from dust and high pressure water jets
- Easy to open catch and unique 180° opening lid
- Suitable for moulded on plugs
- Padlock can be fitted to prevent unauthorised use

### Technical data

- IP66 rating conforms to IEC/ BS EN 60529
- Functional products tested and certified to appropriate British/ IEC Standards. Product range has been independently tested and certified
- Wall Switches Dimension (mm)  
h90 x w90
- Socket Outlets Dimension (mm)  
1 Gang - h103 x w116.5  
2 Gang - h164 x w116.5
- Fused Connection Unit Dimension (mm)  
h103 x w116.5

# Expert tips



01

Suitable for moulded-on plugs:  
Extended enclosure and extra wide gel seal means even moulded on plugs can be accommodated.



02

Padlockable:  
A padlock of up to 5mm diameter shank can be fitted to the enclosure to prevent unauthorised use.



03

Knockouts:  
20mm cable entry knockouts are secure and easily removed by pushing out from the inside of the back box.



04

180°:  
With its unique dual action hinge, the lid of the box can be opened a full 180 degrees for ease of plug insertion and switch operation.



05

Soft sealing:  
The factory fitted soft gel seal fits snugly around power cables to maintain the IP66 rating in use with the lid fully closed.



06

Drill Out:  
If 25mm conduit is needed, then a clearly marked drill out position allows safe and precise use of a 25mm hole saw.



07

Drain:  
The drain feature can be drilled out using a 5mm drill (opening the drain hole will reduce the IP rating of the product).



# IP66

## A peace of mind

Following comprehensive IP66 standard, feel safe to have a tough product protecting you and your wiring accessories.

The rugged good look - it's just a bonus.



10AX 1G  
2 way switch  
**WXPPS12**



10AX 2G  
2 way switch  
**WXPPS22**



20AX 2P 1G  
1 way switch  
**WXPDP84**



20AX 2P 1G  
1 way switch  
with neon  
**WXPDP84N**



20AX 2P 2G  
1 way switch  
**WXPDP842**



10A 1G  
bell push switch  
**WXPPS12B**






# IP66

## For your safety

Designing Hager IP66 range, the focus is really about you. It's about eliminating worries... It's about protecting you and your wiring accessories - the rugged style shows it all.



**13A 1G**  
**WXPS81** unswitched socket  
**WXPSS81** 2P switched socket  
**WXPSS81N** 2P switched socket w/ neon  
**WXPSSU83FO** unswitched fused connection unit w/ flex outlet  
**WXPSSU83FO** 2P switched fused connection unit w/ flex outlet



**13A 2G**  
**WXPS82** unswitched socket  
**WXPSS82** 2P switched socket  
**WXPSS82N** 2P switched socket w/ neon



**15A 1G**  
**WXPSS115** 2P switched socket



**Hager Electro Systems Pte Ltd**

12, Tai Seng Street  
#06-01B, Luxasia Building  
Singapore 534118

Tel : + (65) 6383 1030  
Fax : + (65) 6383 0230  
Email : [www.hager.sg](http://www.hager.sg)

**[hager.sg](http://hager.sg)**