Product Datasheet
JAB310S-IP65

JAB310S-IP65

Technical Features

Electric current

Rated current	100 A
Rated short-time withstand current Icw 1s IEC 60947	2.75 kA

Frequency

Frequency	50 - 60 Hz

Voltage

Rated insulation voltage Ui	800 V
Rated impulse withstand voltage Uimp	8 V

Safety

Ingress Protection (IP) class	IP65

Dimensions

Height	300 mm
Width	300 mm
Depth	200 mm

Installation, mounting

Mounting on	Wall mounting

Sustainability

REACh-SVHC free	Yes