Product Datasheet
HWS4S332D2AE



HWS4S332D2AE

Air Circuit Breaker HWS4 85kA 3200A 3P Drawout LSIG

Technical Features

Electric current	
Rated current	3200 A
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	85 kA
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	85 kA
Rated service breaking capacity Ics under 400 V AC according to IEC 60947-2	85 kA
Endurance	
Electric endurance in number of cycles	8000
Number of mechanical operations	10000
Voltage	
Rated insulation voltage Ui	1000 V
Rated impulse withstand voltage Uimp	12 kV
Type voltage supply	AC
Resistance	
Internal resistance	13.1 µΩ
Architecture	
Number of poles	3
Number of protected poles	3
Device construction type	Drawout
Type of pole	3P
Tripping	
Time of response when closing	40 ms
Power	
Total power loss under IN	496.8 W
Sustainability	
Halogen free	Yes
REACh-SVHC free	Yes
RoHS conform	Yes