Product Datasheet
VB10101T



VB10101T

Vega 4Row 7W 1RCD - 2x6A Ltg. RCBOs

Technical Features

Installation, mounting	
Mounting on	Surface mounting
Suitable for outdoor usage	No
Capacity	
Number of modules	72
Electric current	
Rated current	63 A
Dimensions	
Depth	145 mm
Height	750 mm
Width	370 mm
Number of width units	18
Thickness of sidewall	2.50 mm
Cover, door	
Interlockable	Yes
Door/cover is transparent	Yes
Materials	
RAL code	9010
Colour	Pure white
Material	Polystyrene (PS)
Equipment	
Number of rows	4
Number of rails	4
Extension possible	Yes
Safety	
Impact resistance IK	IK07
Ingress Protection (IP) class	IP40
Protection class	Isolation class II
Compatibility	
Cooker group suitable as power current group	No