Product Datasheet
VB10101TSPD



VB10101TSPD

Vega 4Row 7W 1RCD - 2x6A Ltg. RCBOs SPD

Technical Features

Installation, mounting	
Mounting on	Surface mounting
Functions	
Has protection main switch	No
Overvoltage protection	Yes
Installation, mounting	
Suitable for outdoor usage	No
Configuration	
Number of arc fault detection devices AFDD	0
Capacity	
Number of modules	72
Electric current	
Rated current	63 A
Dimensions	
Depth	145 mm
Height	750 mm
Width	370 mm
Number of width units	18
Thickness of sidewall	2.50 mm
Cover, door	
Interlockable	Yes
Door/cover is transparent	Yes
Materials	
RAL code	9010
Colour	Pure white
Material	Polystyrene (PS)
Connection	
Number of accessible phases	1
Scope of delivery	
Number of earth leakage circuit breaker type A	3
Number of RCCB in enclosure	1
Equipment	
Number of light groups	2
Number of rows	4
With energy meter	No
Number of rails	4
Extension possible	Yes
With bell transformer	No
With socket outlet	No
Safety	
Impact resistance IK	IK07
Ingress Protection (IP) class	IP40
Number of earth leakage switches 300 mA	0