Product Datasheet
EHN110



EHN110

Daily time switch 1 channel, 3 modules

Technical Features

Equipment

Number of channels	1

Frequency

Frequency	50 - 50 Hz

Power

Power consumption during operation	0.9 W
230 V incandescent and halogen lamp	1100 W
Power incandescent lamp	900 - 900 W

Functions

Number of function channels	1

Connection

Number of contacts	1
Cross-section flexible conductor	0.5 - 6 mm²
Cross-section rigid conductor	0.5 - 6 mm²

Use conditions

Operating temperature	-20 - +55 °C

Capacity

Number of modules	3

Dimensions

Height	90 mm
Width	54 mm
Depth	60 mm

Texts

Switch mode	Change-over contact
Installation mode	For mounting on DIN rail

Electric current

Max. power (cos phi 0,6)	3 A

Endurance

Electrical durability at nominal load in AC1 in operating cycles	50000

Texts

Type of connection	With screw terminals

Voltage

Rated operational voltage Ue	230 - 240 V

Power

Power dissipation at full load	1 W

Settings

Programme cycles	Programme cycle: 24 hours
Shortest switching time	15 min

Lighting

LED lamp power	180 W

Use

Type of cycle	Daily