


# Product Datasheet

## 41491606



41491606

SCHUKO soc.out.,lab.field,enhncd contact prot.,screw-in lift term.,B.3/B.7,ant.

### Technical Features

#### Electric current

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

#### Voltage

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

|                 |             |
|-----------------|-------------|
| Nominal voltage | 250 - 250 V |
|-----------------|-------------|

#### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

#### Materials

|        |            |
|--------|------------|
| Colour | Anthracite |
|--------|------------|

|          |      |
|----------|------|
| RAL code | 7021 |
|----------|------|

|                |      |
|----------------|------|
| Surface finish | Matt |
|----------------|------|

|          |               |
|----------|---------------|
| Material | Thermoplastic |
|----------|---------------|

|           |           |
|-----------|-----------|
| Treatment | Untreated |
|-----------|-----------|

#### Dimensions

|        |       |
|--------|-------|
| Height | 71 mm |
|--------|-------|

|       |       |
|-------|-------|
| Width | 71 mm |
|-------|-------|

|                 |   |
|-----------------|---|
| Number of units | 1 |
|-----------------|---|

|                |       |
|----------------|-------|
| Built-in depth | 32 mm |
|----------------|-------|

#### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

#### Connectivity

|                    |                |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

|               |                                 |
|---------------|---------------------------------|
| Mounting type | Screw mounting<br>Claw mounting |
|---------------|---------------------------------|

#### Equipment

|                                   |        |
|-----------------------------------|--------|
| Connector/plug type socket outlet | SCHUKO |
|-----------------------------------|--------|

|                        |    |
|------------------------|----|
| Rotated central insert | No |
|------------------------|----|

|                 |    |
|-----------------|----|
| With hinged lid | No |
|-----------------|----|

|                                 |    |
|---------------------------------|----|
| With round protective earth pin | No |
|---------------------------------|----|

|                  |    |
|------------------|----|
| With signal lamp | No |
|------------------|----|

|           |    |
|-----------|----|
| With lock | No |
|-----------|----|

#### Accessories

|                     |     |
|---------------------|-----|
| Has labelling field | Yes |
|---------------------|-----|

#### Capacity

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

#### Safety

|                                  |     |
|----------------------------------|-----|
| With enhanced contact protection | Yes |
|----------------------------------|-----|

|                      |      |
|----------------------|------|
| Impact resistance IK | IK05 |
|----------------------|------|

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

#### Functions

|                           |    |
|---------------------------|----|
| With orientation lighting | No |
|---------------------------|----|

|                        |    |
|------------------------|----|
| With function lighting | No |
|------------------------|----|

#### Texts

|         |                 |
|---------|-----------------|
| Imprint | Without imprint |
|---------|-----------------|

|       |                     |
|-------|---------------------|
| Cover | Central cover plate |
|-------|---------------------|

|            |                             |
|------------|-----------------------------|
| Protection | Enhanced contact protection |
|------------|-----------------------------|

|                    |                              |
|--------------------|------------------------------|
| Type of connection | With screw-in lift terminals |
|--------------------|------------------------------|

|           |                      |
|-----------|----------------------|
| Labelling | With labelling field |
|-----------|----------------------|

Product Datasheet

41491606

|                |  |     |
|----------------|--|-----|
| Suitable for   |  |     |
| S.x/B.x        |  |     |
| Sustainability |  |     |
| RoHS conform   |  | Yes |