

# ZODZ2.E66583 - POSITIONING DEVICES - COMPONENT

## Positioning Devices - Component

See General Information for Positioning Devices - Component

### BOCCHIOTTI SPA

Via dei Valtorta 45  
20127 Milano, MI ITALY

E66583

### Positioning Devices Investigated to ANSI/UL 1565

Catalog No.	Maximum Use Temp °C(°F)
<b>PP Slotted Flexible Ducts (gray color) "Dinosauro Series"</b>	
DN-A 25G (a)	65 (149)
DN-A 35G (a)	65 (149)
DN-A 45G (a)	65 (149)
DN-AL (a).	65 (149)
DN-AM (a)	65 (149)
DN-AS (a)	65 (149)
<b>PP Slotted Flexible Ducts (white, natural color) "Dinosauro Series"</b>	
DN-10A W (b)	80 (176)
DN-20A W (b)	80 (176)
DN-30A W (b)	80 (176)
DN-40A W (b)	80 (176)
DN-A 25 W (b)	80 (176)
DN-A 35 W (b)	80 (176)
DN-A 45 W (b)	80 (176)
<b>PVC Ducts "T1"</b>	
T1 Series, followed by 15x18, 15x30, 15x40, 15x60, 25x30, 25x40, 25x60, 25x80, 25x100, 40x40, 40x60, 40x80, 40x100, 60x40, 60x60, 60x80, 60x100, 75x125, 80x40, 80x60, 80x80, 80x100, 100x40, 100x60, 100x80, 100x100, 100x125, 120x60, 120x80 or, 150x100 (c) (f)	50 (122)
<b>PVC Slotted Ducts "T1-D"</b>	

<b>T1-D Series, followed by 25x40, 25x60, 25x80, 40x40, 40x60, 40x80, 40x100, 60x40, 60x60, 60x80, 60x100, 80x60, 80x80, 80x100, 100x60, 100x80, 100x100 or 120x80 (c) (e)</b>	50 (122)
<b>PVC Ducts "T1-E"</b>	
<b>T1-E Series, followed by 15x18, 15x30, 15x40, 15x60, 25x30, 25x40, 25x60, 25x80, 25x100, 40x40, 40x60, 40x80, 40x100, 60x40, 60x60, 60x80, 60x100, 75x125, 80x40, 80x60, 80x80, 80x100, 100x40, 100x60, 100x80, 100x100, 100x125, 120x60, 120x80 or 150x100 (c) (f)</b>	50 (122)
<b>PVC Ducts "T1-EF"</b>	
<b>T1-EF Series, followed by 15x60, 25x60, 25x80, 25x100, 40x60, 40x80, 40x100, 60x60, 60x80, 60x100, 75x125, 80x60, 80x80, 80x100, 100x60, 100x80, 100x100, 100x125, 120x60, 120x80 or 150x100 (c) (f)</b>	50 (122)
<b>Plastic Ducts (narrow, light grey) "T1-EH"</b>	
<b>T1-EH 100x100 LG</b>	50 (122)
<b>T1-EH 100x50 LG</b>	50 (122)
<b>T1-EH 100x75 LG</b>	50 (122)
<b>T1-EH 37.5x37.5 LG</b>	50 (122)
<b>T1-EH 37.5x50 LG</b>	50 (122)
<b>T1-EH 37.5x75 LG</b>	50 (122)
<b>T1-EH 50x100 LG</b>	50 (122)
<b>T1-EH 50x50 LG</b>	50 (122)
<b>T1-EH 50x75 LG</b>	50 (122)
<b>T1-EH 75x100 LG</b>	50 (122)
<b>T1-EH 75x50 LG</b>	50 (122)
<b>T1-EH 75x75 LG</b>	50 (122)
<b>PVC Ducts "T1-EN"</b>	
<b>T1-EN Series, followed by 25x40, 25x60, 25x80, 25x100, 40x40, 40x60, 40x80, 40x100, 60x40, 60x60, 60x80, 60x100, 80x40, 80x60, 80x80, 80x100, 100x40, 100x60, 100x80, 100x100, 120x60, 120x80, 150x100. (c)(e)</b>	50 (122)
<b>PVC Ducts "T1-F"</b>	
<b>T1-F Series, followed by 15x60 25x80, 25x100, 40x80, 40x100, 60x80, 60x100, 80x80, 80x100, 100x80, 100x100, 120x60, 120x80 or 150x100 (c) (f)</b>	50 (122)
<b>Plastic Ducts (open, light grey) "T1-H"</b>	
<b>T1-H 100x100 LG</b>	50 (122)
<b>T1-H 100x50 LG</b>	50 (122)
<b>T1-H 100x75 LG</b>	50 (122)
<b>T1-H 25x37.5 LG</b>	50 (122)

<b>T1-H 25x50 LG</b>	50 (122)
<b>T1-H 25x75 LG</b>	50 (122)
<b>T1-H 37.5x37.5 LG</b>	50 (122)
<b>T1-H 37.5x50 LG</b>	50 (122)
<b>T1-H 37.5x75 LG</b>	50 (122)
<b>T1-H 50x100 LG</b>	50 (122)
<b>T1-H 50x50 LG</b>	50 (122)
<b>T1-H 50x75 LG</b>	50 (122)
<b>T1-H 75x100 LG</b>	50 (122)
<b>T1-H 75x50 LG</b>	50 (122)
<b>T1-H 75x75 LG</b>	50 (122)
<b>PVC Ducts "T1-N"</b>	
<b>T1-N Series, followed by 25x30, 25x40, 25x60, 25x80, 25x100, 40x40, 40x60, 40x80, 40x100, 60x40, 60x60, 60x80, 60x100, 80x40, 80x60, 80x80, 80x100, 100x40, 100x60, 100x80, 100x 100, 120x60, 120x80, 150x100 (c) (e)</b>	50 (122)
<b>PC/ABS Wiring Ducts (all color) "T1-ZH"</b>	
<b>T1-ZH 100X100</b>	65 (149)
<b>T1-ZH 100X40</b>	65 (149)
<b>T1-ZH 100X60</b>	65 (149)
<b>T1-ZH 100X80</b>	65 (149)
<b>T1-ZH 120X60</b>	65 (149)
<b>T1-ZH 120X80</b>	65 (149)
<b>T1-ZH 25X25</b>	65 (149)
<b>T1-ZH 25X40</b>	65 (149)
<b>T1-ZH 25X60</b>	65 (149)
<b>T1-ZH 25X80</b>	65 (149)
<b>T1-ZH 30X100</b>	65 (149)
<b>T1-ZH 30X40</b>	65 (149)
<b>T1-ZH 30X60</b>	65 (149)
<b>T1-ZH 30X80</b>	65 (149)
<b>T1-ZH 40X100</b>	65 (149)
<b>T1-ZH 40X25</b>	65 (149)
<b>T1-ZH 40X40</b>	65 (149)
<b>T1-ZH 40X60</b>	65 (149)

<b>T1-ZH 40X80</b>	65 (149)
<b>T1-ZH 60X100</b>	65 (149)
<b>T1-ZH 60X40</b>	65 (149)
<b>T1-ZH 60X60</b>	65 (149)
<b>T1-ZH 60X80</b>	65 (149)
<b>T1-ZH 80X100</b>	65 (149)
<b>T1-ZH 80X25</b>	65 (149)
<b>T1-ZH 80X40</b>	65 (149)
<b>T1-ZH 80X60</b>	65 (149)
<b>T1-ZH 80X80</b>	65 (149)
<b>PVC Ducts "TD"</b>	
<b>TD Series, followed by 25x25, 25x50, 37.5x25, 37.5x50, 37.5x75, 50x37.5, 50x50, 50x75, 75x50, 75x75, 75x125, 100x50, 100x75, 100x125, 125x50 or 125x75 (c)(e)</b>	50 (122)
<b>PVC Ducts "TPD"</b>	
<b>TPD Series followed by 25x25, 25x50, 37,5x25, 37,5x50, 50x37,5, 50x50, 75x50, 100x50, 125x50 (d)(e)</b>	50 (122)
<b>PVC Ducts "TS"</b>	
<b>TS Series, followed by 15x18, 15x30, 15x40, 15x60, 25x30, 25x40, 25x60, 25x80, 25x100, 40x40, 40x60, 40x80, 40x100, 60x40, 60x60, 60x80, 60x100, 75x125, 80x40, 80x60, 80x80, 80x100, 100x40, 100x60, 100x80, 100x100, 100x125, 120x60, 120x80, 150x100 (c)</b>	50 (122)
<b>PVC Ducts "TS-H"</b>	
<b>TS-H Series, followed by 15x18, 15x30, 15x40, 15x60, 25x30, 25x40, 25x60, 25x80, 25x100, 40x40, 40x60, 40x80, 40x100, 60x40, 60x60, 60x80, 60x100, 75x125, 80x40, 80x60, 80x80, 80x100, 100x40, 100x60, 100x80, 100x100, 100x125, 120x60, 120x80, 150x100 (c)</b>	50 (122)
<b>PC/ABS Wiring Ducts (all color)</b>	
<b>TD-HF 100X50# (g)</b>	-
<b>TD-HF 100X75# (g)</b>	-
<b>TD-HF 125X50# (g)</b>	-
<b>TD-HF 125X75# (g)</b>	-
<b>TD-HF 25X25# (g)</b>	65 (149)
<b>TD-HF 25X37# (g)</b>	-
<b>TD-HF 25X50# (g)</b>	-
<b>TD-HF 37X100# (g)</b>	-
<b>TD-HF 37X37# (g)</b>	-
<b>TD-HF 37X50# (g)</b>	-

<b>TD-HF 37X75# (g)</b>	-
<b>TD-HF 50X37# (g)</b>	-
<b>TD-HF 50X50# (g)</b>	-
<b>TD-HF 50X75# (g)</b>	-
<b>TD-HF 75X50# (g)</b>	-
<b>TD-HF 75X75# (g)</b>	-

(a) - Ducts use raw materials rated 94V-0 or 94V-2. Ducts with handling strips use materials rated 94V-0 for the ducts and 94V-2 for the handling strips.

(b) - The Beiersdorf double sided tape Tesa 4965 may be used as the sole means of securement when it is used to affix these cable ducts to enamel painted metal and cellulose sheet impregnated with phenolic and melamine resins type surfaces.



(c) - Suffixed with G denoting color grey, W denoting color white, BL denoting color blue or A denoting color black.

(d) - Suffixed with G denoting color grey

(e) - May be followed by SB suffix denoting no predrilled mounting holes (Solid Bottom)

(f) - May be followed by VK suffix denoting US design Bottom drilling (in inches) or SB suffix denoting no predrilled mounting holes (Solid Bottom)

(g) - # Indicates the color

Marking: Company name or tradename "E66583" or trademark  , catalog or model number, the Recognized Component Mark,  and, if published with the product, the product's maximum and minimum operating temperature, minimum installation temperature if below 0°C, minimum and maximum bundle diameter, loop tensile strength, type designation and/or declared mechanical strength on the product or on the smallest unit container in which the product is packaged.

Last Updated on 2019-02-27

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2019 UL LLC"