

# STATEMENT OF TEST RESULTS

Reference: STR/B21/2017

**Product:** socket-outlets (2-pole)

**Tested by request of:** AB Plast s.r.l. - Hager Group  
Via del Artigianato n°6  
25080 MAZZANO (BS)  
Italy

**Manufactured at (name and place):** Berker Polska Sp.z.o.o  
Ul. Sredzka 19  
62-035 KORNIK  
Poland

**Rating and principal characteristics:** See page 2

**Preliminary visit carried out by:** DEKRA Certification B.V.  
Meander, 1051  
PO Box 5185  
6825 MJ ARNHEM  
Netherlands

**Trade mark (if any):** HAGER

**Model/Type ref:** French Socket - Gallery Series (see appendix)

**Additional information (if any):** /

A sample of the product has been tested and found to be in conformity with the current (HD/EN and equivalent national standard, number and edition)

IEC 60884-1:2002 + A1:2006 + A2:2013, NBN C 61-112-1:2017, NF C61-314:2008 + A1:2010

as shown in the test report 628432.01

This statement is the result of testing a sample of the product submitted, in accordance with the provisions of the relevant specific standard.

This statement of the test results has been established by a body which participates directly in the CENELEC Certification Agreement (CCA) of September 11th, 1973 as revised on March 29th, 1983, on September 3rd, 2004 and on April 18<sup>th</sup>, 2007 (including addendum 1 dated July 1984, addendum 2 dated March 1987, addendum 3 dated September 1989 and addendum 4 dated March 1995). Any other body participating in the CCA will take this Notification as a basis for granting a national mark of conformity or a national approval as specified in the CCA.

Brussels, 08/11/2017

  
C. LANA  
Certification Manager



**Ratings:**

rated voltage (Un)	:	250 Vac
rated current (In)	:	16 A
terminals	:	screwless, rigid and flexible
earthing	:	with and without earthing pin
design	:	design A
		rewirable
standard sheet	:	V of NBN C 61-112-1
		I of NF C-61-314
		IIIa of NF C 61-314
existence of shutters	:	with shutters
degree of protection	:	IP 20
method of mounting	:	flush type
markings	:	are shown on the body



0 1 2 3 4 5

Technical code	Description	Rated current (A)	Rated Voltage (V)	Freq. (Hz)	Type of terminal	IP
WXF100	French socket 2P+T screwless	16A	250V	50	Screwless	IP20
WXF102	French socket 2P screwless	16A	250V	50	Screwless	IP20
WXF105	French socket refurbishing 2P+T screwless	16A	250V	50	Screwless	IP20
WXA450	Gallery frame 2M (NF mark)	NA	NA	NA	NA	NA



0 1 2 3 4 5