

# LICENCE

No. 21116

Issued to:

Applicant:

**AB Plast s.r.l. - Hager Group**

**Via del Artigianato n°6**

**25080 MAZZANO (BS)**

**Italy**

Licensee:

**AB Plast s.r.l. - Hager Group**

**Via del Artigianato n°6**

**25080 MAZZANO (BS)**

**Italy**



Product : rocker switches  
Trade name(s) : HAGER  
Type(s)/model(s) : Series Gallery (see appendix)

The product and any acceptable variation thereto is specified in the annex to this licence and the documents therein referred to.

SGS CEBEC hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard specified in annex
- an inspection of the production location
- a certification agreement with the number 1447

SGS CEBEC hereby grants the right to use the CEBEC certification mark

The CEBEC certification mark may be applied to the product as specified in this licence for the duration of the CEBEC certification agreement and under the conditions of the CEBEC certification agreement.

This licence is issued on: 29/01/2019

ir. C. Lana,  
Certification Manager

© Only integral publication of this certificate, including the annex, is allowed

This certificate is only valid combined with the publication on the following web address: [www.sgs.com/ee](http://www.sgs.com/ee)



## SPECIFICATION OF THE CERTIFIED PRODUCT

### Product data

Product	:	rocker switches
Trade name(s)	:	HAGER
Type(s)/Model(s)	:	Series Gallery (see appendix)
rated voltage (Un)	:	250 Vac
rated current (In)	:	16 AX
pattern no(s).	:	2
method of actuating	:	rocker
terminals	:	screwless (rigid and flexible)
method of installation	:	design A rewirable
method of application	:	for trunking
degree of protection	:	IP 20
certification mark	:	complies with the requirements
markings	:	are shown on the body

### Additional information

Switch intended to be used in the trunking systems:

45-trunking GBD, GBA & TA-C  
 Trunkings cover adaptors LF, BRx  
 Skirting SL  
 45-Pole DA & DB  
 Desk module Easybloc

See Appendix

## TESTS

### Test requirements

NBN EN 60669-1 based on EN 60669-1:1999 + A1:2002 + A2:2008

### Test results


The test results are laid down in test report ref. 630005.01

**Conclusion**

The examination proved that all certification requirements were met.

Reviewed by, project leader : Luigi Zanutto - 29/01/2019

Certification Manager :



*[Signature]* 2019-01-29

**FACTORY LOCATION(S)**

Berker Polska Sp.z.o.o  
Ul. Sredzka 19  
62-035 KORNIK  
Poland

Technical code	Pattern no.	Description	Rated current	Rated Voltage	Freq (Hz)	Type of terminal	IP
WXF436B	2	2 Poles switch white	16AX	250V	50	Screwless	IP20
WXF436T	2	2 Poles switch alu	16AX	250V	50	Screwless	IP20
WXF436N	2	2 Poles switch Black	16AX	250V	50	Screwless	IP20

0 1 2 3 4 5

