

Rotary dimmer 400 W with cover plate

Order-No.: 2819...

Operation- and Assembly Instructions

1 Safety instructions

Electrical equipment may only be installed and fitted by electrically skilled persons.

Failure to observe the instructions may cause damage to the device and result in fire and other hazards.


Danger of electric shock. Always disconnect before carrying out work on the devise or load. At the same time, take into account all circuit breakers that supply dangerous voltage to the device or load.

Danger of electric shock. Device is not suitable for disconnection from supply voltage. The load is not electrically isolated from the mains even when the device is switched off.

Do not connect any electronic lamps, e.g. switchable or dimmable compact fluorescent lamps or LED lamps. Device can be damaged.

These instructions are an integral part of the product, and must remain with the end customer.

2 Device components



picture 1: Device components

- (1) Dimmer
- (2) Cover
- (3) Control button
- (4) Fuse holder
- (5) Screw terminals

3 Function

Intended use

- Switching and dimming incandescent lamps and HV halogen lamps
- Suitable for mixed operation up to the specified output (see chapter 6.1. Technical data)
- Installation in appliance box to DIN 49073
- i No operation with changeover switch possible.



i No operation with transformers possible.

Product characteristics

- Phase cut-on dimming principle
- Short-circuit protection through fine-wire fuse
- Flickering of the connected lamps due to undershoot of the specified minimum load or through centralised pulses from the power stations and soft humming of the device due to the radio interference suppressor. These are not device faults.

4 Operation

i Switching and dimming are performed by turning the control button.

Switching the light on and increasing the brightness

Turn control button to the right.

Switching the light off

Turn control button all the way to the left.

5 Information for electrically skilled persons

5.1 Fitting and electrical connection




DANGER!

Electrical shock when live parts are touched.

Electrical shocks can be fatal.

Before carrying out work on the device or load, disengage all the corresponding circuit breakers. Cover up live parts in the working environment.

Connecting and mounting the dimmer



picture 2: Connection diagram

- Connect the dimmer (1) according to the connection diagram (picture 2).
- Mount the dimmer in the accessory socket.
- Mount the cover (2).
- Attach the control button (3).



6 Appendix

6.1 Technical data Rated voltage Mains frequency Ambient temperature	AC 230 V ~ 50 Hz +5 +25 °C
Connected load at 25 °C Incandescent lamps HV halogen lamps	60 400 W 60 400 W
Power reduction Surface mounting per 5°C in excess of 25°C	-5 % -10 %

when installed in wooden or dry construction
walls
when installed in multiple combinations
-15 %
-20 %

Connection

Single stranded 0.5 ... 2.5 mm²

Power boosters

See power booster instructions
Fine-wire fuse

D 1.6 H 250



The symbols used to label the dimmer load shows the load type that can be connected to a dimmer and the electric behaviour of a load: R = ohmic

6.2 Troubleshooting

The device cannot be switched on. Or: The device switches the load off and cannot be switched on again.

Check fine-wire fuse and replace if necessary. Use only original fuses.

6.3 Warranty

We reserve the right to make technical and formal changes to the product in the interest of technical progress.

Our products are under guarantee within the scope of the statutory provisions.

If you have a warranty claim, please contact the point of sale or ship the device postage free with a description of the fault to the appropriate regional representative.

Berker GmbH & Co. KG

Klagebach 38 58579 Schalksmühle/Germany Telefon + 49 (0) 2355/905-0 Telefax + 49 (0) 2355/905-111 www.berker.de