

UKCA DECLARATION OF CONFORMITY No. UKCA 21_3120_12_21

We	Hager Electro SAS BP3 67215 OBERNAI CEDEX - FRANCE
Declare that the product(s)	
Designation	Add On Blocks
Type reference(s)	B Range
Trademark	Hager
is (are) in conformity with the relevant United	Kingdom legislation:
- SI 2012/3032 Restriction of the Use amended)	e of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012 (as
- SI 2016/1091 Electromagnetic Comp	patibility (EMC) Regulations 2016 (as amended)
- SI 2016/1101 Electrical Equipment (s	safety) Regulations 2016 (as amended)
Standard(s) and/or relevant document(s) to we standard number + relevant amendments together with the edition BS EN 61009-1:2012+A1+A2+A11+A12	on dates
BS EN 61009-2-1:1994+A1998	
BS EN IEC 63000:2018	
If applicable, mention here for radio products, the dat	ta about notified body. See RE legislation - Annex VI - point 7
	under the sole responsibility of the manufacturer.
On behalf of Hager Electro SAS	Function of -tt
Name of signatory Eric Boivin	Function of signatory Certification manager
Place and date of issue Obernai, FR 06/12/2021	Signature

DMS055162 Version 3 1/6



No. UKCA 21_3120_12_21

Type references

Residual current units range

			Rated resi	idual current	and operating	characteristic														
			10 mA		30 mA		100 mA				300 mA			500 mA				1A		
In	Poles	Series	A	AC	A	AC	A	AC	AS	ACS	A	AC	AS	ACS	A	AC	AS	ACS	AS	ACS
	1P+N				BD225N	BD226N														
	2P	Neutral on the Right	BC225N	BC226N	BDA225N BDH225N	BDC225N	BE225N	BE226N			BF225N	BF226N			BG225N	BG226N				
	3Р				BD325N BDH325N BDA325E	BD326N BDC325E	BE325N	BE326N			BF325N	BF326N			BG325N	BG326N				
	3P+N				BD425N BDH425N	BD426N	BE425N	BE426N			BF425N	BF426N			BG425N	BG426N				
25A	1P+N				BD225	BD226			1						ALL EN					
	2P		BC225	BC226	BDA225 BDH225 BDA225P	BDC225 BDC226P	BE225 BEA225P	BE226 BEC226P			BF225 BFA225P	BF226 BFC226P			BG225 BGA225P	BG226 BGC226P				
	3P	Neutral on the Left			BD325 BDH325 BDA325P	BD326 BDC326P	BE325 BEA325P	BE326 BEC326P			BF325 BFA325P	BF326 BFC326P			BG325 BGA325P	BG326 BGC326P				
	3P+N				BD425 BDH425 BDA425P	BD426 BDC426P	BE425 BEA425P	BE426 BEC426P				BF426 BFC426P			BG425 BGA425P	BG426 BGC426P				

DMS055162 Version 3 2/6



No. UKCA 21_3120_12_21

Type references

Residual current units range

			Rated	residual	current and	operating ch	aracteristic													
			10 mA		30 mA		100 mA				300 mA			500 mA				1A		
In	Poles	Series	A	AC	A	AC	Α	AC	AS	ACS	А	AC	AS	ACS	Α	AC	AS	ACS	AS	ACS
	1P+N				BD240N	BD241N														
	2P				BDA240N BDH240N	BDC240N					BF240N	BF241N								
	3P	Neutral on the Right			BD340N BDH340N BDA340E	BD341N BDC340E					BF340N	BF341N								
	3P+N				BD440N BDH440N	BD441N					BF440N	BF441N								
40 A	1P+N				BD240	BD241														
	2P				BDA240 BDH240 BDA240P	BDC240 BDC241P	BEA240P	BEC241P			BF240 BFA240P	BF241 BFC241P			BGA240P	BGC241P				
	3P	Neutral on the Left			BD340 BDH340 BDA340P	BD341 BDC341P	BEA340P	BEC341P			BF340 BFA340P	BF341 BFC341P			BGA340P	BGC341P				
	3P+N				BD440 BDH440 BDA440P	BD441 BDC441P	BEA440P	BEC441P			BF440 BFA440P	BF441 BFC441P			BGA440P	BGC441P				

DMS055162 Version 3 3/6



No. UKCA 21_3120_12_21

Type references

Residual current units range

			Rat	ed r	residual curr	ent and ope	rating chara	cteristic													
			10	mA	30 mA		100 mA				300 mA				500 mA			2000	1A	72	
In	Poles	Series	A	A C	A	AC	A	AC	AS	ACS	A	AC	AS	ACS	A	AC	AS	ACS	AS	ACS	
	1P+N	1			BD263N	BD264N								34.11	1900				E I		
	2P				BDA263N BDH263N	BDC263N	BE263N	BE264N	BN263N	BN264N	BF263N	BF264N	BP263N	BP264N	BG263N	BG264N	BR263N	BR264N	BS263N	BS264N	
	3P	Neutral on the Right	the	he		BD363N BDH363N BDA363E	BD364N BDC363E	BE363N	BE364N	BN363N	BN364N	BF363N	BF364N	BP363N	BP364N	BG363N	BG364N	BR363N	BR364N	BS363N	BS364N
	3P+N				BD463N BDH463N	BD464N	BE463N	BE464N	BN463N	BN464N	BF463N	BF464N	BP463N	BP464N	BG463N	BG464N	BR463N	BR464N	BS463N	BS464N	
63 A	1P+N				BD263	BD264															
	2P				BDA263 BDH263 BDA263P	BDC263 BDC264P	BE263 BEA263P	BE264 BEC264P	BN263 BNA263P	BN264 BNC264P	BF263 BFA263P	BF264 BFC264P	BP263 BPA263P	BP264 BPC264P	BG263 BGA263P	BG264 BGC264P	BR263 BRA263P	BR264 BRC264P	BS263 BSA263P	BS264 BSC264P	
	3P	Neutral on the Left			BD363 BDH363 BDA363P	BD364 BDC364P	BE363 BEA363P	BE364 BEC364P	BN363 BNA363P	BN364 BNC364P	BF363 BFA363P	BF364 BFC364P	BP363 BPA363P	BP364 BPC364P	BG363 BGA363P	BG364 BGC364P	BR363 BRA363P	BR364 BRC364P	BS363 BSA363P	BS364 BSC364P	
	3P+N				BD463 BDH463 BDA463P	BD464 BDC464P	BE463 BEA463P	BE464 BEC464P	BN463 BNA463P	BN464 BNC464P	BF463 BFA463P	BF464 BFC464P	BP463 BPA463P	BP464 BPC464P	BG463 BGA463P	BG464 BGC464P	BR463 BRA463P	BR464 BRC464P	BS463 BSA463P	BS464 BSC464P	

DMS055162 Version 3 4/6



No. UKCA 21_3120_12_21

Evidence (s)

Documents listed below have been used in order to establish the conformity to the essential requirements of the relevant legislation

Engineering Quality / Certification Telford
Yes
BS EN 61009-1:2012 BS EN 61009-2-1:1994
Yes
Designated Before 2016
DMS034433 followed using case 1 of Hager Group method:
Designated standard used
STR 2546/IMQ IT 17381
No
See Hager Website
None

DMS055162 Version 3 5/6



No. UKCA 21_3120_12_21

Evidence (s)

Documents listed below have been used in order to establish the conformity to the essential requirements of the relevant legislation

Designated Standards

Designated standard UKCA Electrical Equipment (Safety) Regulations 2016:

S.I. 2016 No. 1101	EN 61009-1:2012	Residual current operated circuit-breakers with integral overcurrent protection for household and similar uses (RCBOs) - Part 1: General rules	01/01/2021	0009/21
S.I. 2016 No. 1101	EN 61009-2-1:1994	Residual current operated circuit-breakers with integral overcurrent protection for household and similar uses (RCBO's) - Part 2-1: Applicability of the general rules to RCBO's functionally independent of line voltage	01/01/2021	0009/21

Designated standard UKCA Electromagnetic Compatibility Regulations 2016:

S.I. 2016	EN 61009-1:2012	Residual current operated circuit-breakers with integral	01/01/2021	0007/21
No. 1091		overcurrent protection for household and similar uses		
		(RCBOs) - Part 1: General rules		

Designated standard UKCA RoHS:

S.I. 2012	EN IEC 63000:2018	Technical documentation for the assessment of electrical	01/01/2021	0037/21
No. 3033		and electronic products with respect to the restriction of		
		hazardous substances		

DMS055162 Version 3 6/6