# :hager



Motorised source changeover switch 125A - 630A

### HIC4xxE



### **Preliminary operations**

Check the following upon delivery and after removal of the packaging:

- Packaging and contents are in good condition.
- The product reference corresponds to the order.
- Contents should include:
  - 1 x motorised changeover switch
  - 1 x emergency handle and fixing clip
  - 1 x quickstart instruction sheet.

### **Accessories**

- Bridging bars and connection kits.
- Terminal shrouds.
- Terminal shield.
- · Voltage sensing kit.
- HZI911 interface.
- Current transformers.

 Plug-in optional modules: RS485 MODBUS communication, 2 inputs/2 outputs, Ethernet communication, Ethernet communication + RS485 JBUS/MODBUS gateway, Analogue outputs, Pulse outputs.

This quick start is intended for personnel trained in the installation and commissioning of this product. For further details refer to the product instruction manual available on the hager website.


- This product must always be installed and commissioned by qualified and approved personnel.
- Maintenance and servicing operations should be performed by trained and authorised personnel.
- Do not handle any control or power cables connected to the product when voltage may be, or may become present on the product, directly through the mains or indirectly through external circuits.

- Always use an appropriate voltage detection device to confirm the absence of voltage.
- Ensure that no metal objects are allowed to fall in the cabinet (risk of electrical arcing).

Failure to observe good enginering practises as well as to follow these safety instructions may expose the user and others to serious injury or death.




Risk of electrocution, burns or injury to persons and/or damage to equipment. Risk of damaging the device. In case the product is dropped or damaged in any way it is recommended to replace the complete product.





6LE001133A.d







### Orientation










	125A	160A	200A	250A	315A	400A	500A	630A		
		4P								
J1		34		35			34			
М	150			210			270			
T	36			50			65			
С			24	14			320			
U		20		25 35			32	45		
W		9			11			13		
CA		10			15		2	0		

# 

## Door cut-out for front panel




### 2. Power terminal connections

Use terminal lugs, rigid or flexible busbars.

		125A	160A	200A	250A	315A	400A	500A	630A
Minimum Cu cable section ( at Ith	(mm²)	3	5	50	95	120	185	2x95	2x120
Minimum Cu busbar section (mm²) at Ith		-						2x30x5	2x40x5
Maximum Cu cable section	(mm²)	50	95	120	150	24	40	2x185	2x300
Maximum Cu busbar width (mm)		25			32			50	
Type of screw		M8			M10			M12	
Recommended tightening (torque	(N.m)		8,3		20			40	
Maximum tightening (torque	(N.m)	13			26			45	

### 3. CONTROL/COMMAND terminals

Ensure that the product is in Manual Mode.



### 4. Power supply, sensing and control wiring

Use cables with 1,5 to 2,5 mm<sup>2</sup> section.

Screw M3

Tightening torque: min.: 0.5 Nm - max.: 0.6 Nm




### ATS Power supply input II

Power supply II - L Power supply II - N 208-277 VAC ±20%: 50/60 Hz

### ATS Voltage sensing input Source supply II

S II - Phase 1 S II - Phase 2 S II - Phase 3 575 VAC (ph-ph) maxi S II - Neutral 332 VAC (ph-n) maxi




To option module (-)/Common Progr. inputs (208-209) To option module (+)

### Genset Start/stop

2 Alternate source

NC Common NO



### ATS Power supply input I

Power supply I - L Power supply I - N 208-277 VAC ±20%: 50/60 Hz

### ATS Voltage sensing input Source supply I

SI-Phase 1 SI-Phase 2 SI-Phase 3 575 VAC (ph-ph) maxi SI-Neutral 332 VAC (ph-n) maxi

ATS Module control inputs (programmable)


ATS Module output control (programmable)


Remote interface RJ45 to HZI911






1 Preferred source






- Programmable output contact, by default set to ATS product available Normally open
- 2 to 5 programmable inputs 1-4
- 6 and 7 programmable inputs 5-6
- Aux. supply (207/210) to be used with optional I/O modules
- © Contact "Start/Stop Genset": if S1 is not available the NC contact (71-72) is closed
- Contact "Start/Stop Genset": if S1 is not available the NO contact (71-74) is open
- ② Option module slots 1 to 4
- Current Transformer incoming cable connections
- Voltage sensing inputs
- Power supply inputs



### 5. Check

Whilst in manual mode, check the wiring and if ok power up the product.











LED Green = "Power" : ON

LED Red = "Manuel/Defaut": ON





The product is delivered with default setting values based on most used customer application requirements. The minimum configuration parameters that must be programmed are the type of network and application together with the voltage and frequency nominal values.

### **Network parameters**

3 phases/4 wire

Ensure that the Default Network Setting and Application match the installation or change accordingly before using Auto Configuration

3BL

3 phases/3 wire

Press 5s	
Go to	1 SETUP
Scroll to	AUTOCONF
Enter code	1000
Set to	YES
Press 60 ms	
LEDs flash	
Save: press 5s	

Note: source I or source II must be available to set by Auto Configuration.

PWR. LEVELS

■ 0000 kVA

0000 kVA

II 0000 kVA

II 0000 kVA

1 phase/2wire

5 TIMERS VALUE

1BL

2 phases/2 wire

2BL

OV.P

OV.P

OV.P HYS

OV.P HYS

# Menus

4NBL

4BL

MEHUS					
1 SETUP		2 VOLT	ſ. LE	VEL	S
NETWORK	4NBL	OV. U	ı		115%
AUTOCONF	NO (7)	OV. U HYS	ı		110%
NEUTRAL	AUT0	UND. U	1		085%
ROT PH.		UND. U HYS	1		095%
NOM. VOLT	400 V	UNB. U	ı		00%
NOM. FREQ	50 Hz	UNB. U HYS	ı		00%
APP	M-G	OV. U		II	115%
PRIO TON	NO <sup>(1)</sup>	OV. U HYS		II	110%
PRIO EON	NO (3)	UND. U		II	085%
PRIO NET	1 (2)	UND. U HYS		II	095%
RETRANS	NO	UNB. U		II	00%
CT PRI	100	UNB. U HYS		II	00%
CT SEC	5				
S1=SW2	NO				
BACKLGHT	INT				
CODE P	1000				
CODE E	0000				
BACKUP	SAVE				

3 FR	EQ. L	EVE	LS
OV. F	1	ī	105%
OV. F HY	S I		103%
UND. F	- 1		095%
UND. F H	YS I		097%
OV. F		II	105%
OV. F HY	S	II	103%
UND. F		II	095%
UND. F H	YS	II	097%

2 phases/3 wire


2NBL

2

1FT	0003 SEC		IN 1		NO		DHCP	
1RT	0180 SEC		IN 2		NO		IP 1-2	
2FT	0003 SEC		IN 3		NO		IP 3-4	
2RT	0005 SEC	(2)	IN 4		NO		GAT1-2	
2AT	0005 SEC	(1)	IN 5		NO		GAT3-4	
2CT	0180 SEC	(1)	IN 6		NO		MSK1-2	
2ST	0030 SEC	(1)	IN 7		NO	(8)	MSK3-4	
ODT	0003 SEC		IN 8		NO	(8)	ADDRESS	
TOT	UNL	(1)	IN 9		NO	(8)	BDRATE	
TOT	0010 SEC	(1)	IN10		NO	(8)	STOP BIT	
T3T	0000 SEC	(1)	IN11		NO	(8)	PARITY	
TFT	UNL	(1)	IN12		NO	(8)		
TFT	0600 SEC	(1)	IN13		NO	(8)		
E1T	0005 SEC	(3)	IN14		NO	(8)		
E2T	UNL	(3)	OUT 1	POP	NO			
E2T	0010 SEC	(3)	OUT 2		NO	(8)		
E3T	0005 SEC	(3)	OUT 3		NO	(8)		
E5T	0005 SEC	(4)	OUT 4		NO	(8)		
E6T	LIM	(4)	OUT 5		NO	(8)		
E6T	0600 SEC	(4)	OUT 6		NO	(8)		
E7T	0005 SEC	(4)	OUT 7		NO	(8)		
LST	0004 SEC	(5)	8 TUO		NO	(8)		
EET	0168 H	(6)	OUT 9		NO	(8)		
EDT	1800 SEC	(6)						

6

### Programming access



Press and hold for 5 s "Validation" pushbutton To Access through the keypad is possible in automatic or manual mode, when the product is in a stable position (I, 0 or II) with at least one supply source available.

Programming is not accessible whilst any cycle sequence is running.

To change the configuration, enter code (factory code = 1000) using navigation pushbuttons **3**. Programming exit: press and hold for 5 s "Validation" pushbutton **7**.

7

NO

192,168.

.002.001

000.000.

.000.000

255.255.

.255.000 005 9600

NONE

8 DATE/TIME

YEAR

DAY

**HOUR** 

MINUTE


SECOND

MONTH

1 SETUP		2 VOLT. LEVELS
NETWORK	4NBL	OV. U 1159
AUTOCONF	NO <sup>(7)</sup>	OV. U HYS I 1109
NEUTRAL	AUT0	UND. U ■ 085%
ROT PH.		UND. U HYS I 095%
NOM. VOLT	400 V	UNB. U ■ 00%
NOM. FREQ	50 Hz	UNB. U HYS ▮ 00%
APP	M-G	OV. U II 1159
PRIO TON	NO <sup>(1)</sup>	OV. U HYS II 1109
PRIO EON	NO (3)	UND. U II 085%
PRIO NET	1 (2)	UND. U HYS II 095%
RETRANS	NO	UNB. U <b>II</b> 00%
CT PRI	100	UNB. U HYS II 00%
CT SEC	5	
S1=SW2	NO	
BACKLGHT	INT	
CODE P	1000	
CODE E	0000	

11	When	"APP"	is set	to"M-G"

- (2) When "APP" is set to "M-M".
- (3) When one of the I/P is set to "EON"
- (4) When one of the I/P is set to "EOF"
- (5) When one of the I/P is set to "LSC"
- (6) When one of the I/P is set to "EES".
- (7) If the product is in manual mode.
- (8) With optional I/O modules.







### 7A. Automatic operation



Ensure that the emergency handle is not inserted in the product and turn the mode selector to the AUT position.



LED Manuel/Default:

OFF

LED green = "Power": LE




LED green "AUT": ON

# 7B. Automatic operation: remote control



Contactor logic

# Order I Order O Order II Position I Position II




Imp. ≥ 60ms
imp.
maintened.

317.
For contactor logic bridge contact 316 with 317.

close contact 312 with

To operate: close the contact corresponding to the desired position.





to the desired position.

To force the product to 0 position "OFF" bridge

# contact 313 with 317. 7C. Manual operation

# LOCAL/REMOTE CTRL AUT





- Manual mode LED indication (yellow steady light when in manual mode).
- Auto mode LED indication (green steady light when in auto mode with no timers running. Green flashing light when in Auto with timers running in the background.
- Cocal/remote control mode LED indication (yellow steady light when in remote control mode). Remote control mode is achieved with the Auto/Manu selector switched to Auto and terminals 312 closed with terminal 317. Remote control orders are received through closing 314 to 316 with 317.
- TEST ON LOAD CONTROL mode LED indication (yellow steady light when in TON mode).
- 5 TEST OFF LOAD CONTROL mode LED indication (yellow steady light when in TOF mode).
- **(6)** Load supply on LED (green when the load is supplied).
- Switch 1 LED position indication (green when in position 1).
- 8 Source supply I availability LED indication (green when supply I voltage is within the set limits).
- ② Zero position LED indication (yellow when in position 0).
- Switch 2 LED position indication (green when in position 2).
- Source supply II availability LED indication (green when supply II voltage is within the set limits).
- LCD display screen: (status, measurement, timers, counters, events, faults, programming...).
- Mode key to shift between operation modes.
- Navigation keys to browse through the product menus without software.
- Fault LED indication (red steady light in case of an ATS controller internal fault. Switch the product from Auto to Manual and back to Auto to reset a fault condition).


- Ready LED indication (green steady light: product is powered and in Auto, watchdog OK, the product is available to changeover).
- Enter key used to enter Prog Mode (press and hold for 5 seconds) and to validate the settings programmed through the keypad.
- ESC key used to escape from a specific screen up to the main menu.
- 19 Lamp test key to check the LED's and LCD screen.
- @ Green LED Indication: power.
- 2 Red LED indication: product unavailable/ manual Mode/fault condition.
- Auto/Manual mode selector switch (key version available as an option).
- Padlocking facility (up to 3 padlocks of dia. 4 - 8mm).
- Emergency manual operation shaft location (accessible only in manual mode).
- Switch position indication window:
   I (On switch I)
   O (Off)
   II (On switch II).

### **Optional modules**

Communication between the software and the product may be done through the Ethernet/ Modbus TCP or Modbus RTU modules that are available as an option. The ETHERNET/MODBUS modules are to be installed in one of the slots provided in the product ATS control unit.

Note: the product may accept a total of 4 additional Input/Output modules offering an additional 8 programmable inputs and 8 programmable outputs. When including a MODBUS module the product accepts a total of 3 I/O modules and when including the ETHERNET module a total of 2 I/O modules.

The Ethernet module includes a built in Web Server for Monitoring, Engine Exerciser Control, Events...









SM201: pulsed O/P



SM202: extended I/O 2xIP 2xO/P



SM203: 4-20 mA



SM211: modbus RS485



SM213: ethernet/modbus TCP simple



SM214: gateway

